

Part Number : 2451350620

Product Description : Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 6 Circuits, Black

Series Number : 245135

Status : Active

Product Category : Power and Signal Cable Assemblies

Documents & Resources

Drawings

Drawing 2451350620_sd.pdf

Packaging Design Drawing 2014400103-PK.pdf

3D Models and Design Files

3D Model 2451350620_stp.zip

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/61/2018 (27 June 2018)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	245135
Description	Mini-Fit Jr.-to-Mini-Fit Jr. Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, 6 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Fit Jr. Both Ends
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
Type	Overmolded Assembly
UPC	889056853910

Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	300V AC

Physical

Cable Length	2.0m
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	201.000/g
Number of Rows	2

Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Insulation Diameter	5.40mm
Wire Size (AWG)	18

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	<u>5559</u>
Mini-Fit Jr. Vertical Headers	<u>5566</u>
Mini-Fit Jr. Right-Angle Headers	<u>5569</u>
Mini-Fit Jr. Dual Row Headers	<u>87427</u>
Mini-Fit BMI Right-Angle Dual Row Headers	<u>42404</u>
Mini-Fit BMI Vertical Dual Row Headers	<u>42440</u>
Mini-Fit BMI Right-Angle Dual Row Headers	<u>43810</u>
Mini-Fit BMI Vertical Dual Row Headers	<u>44068</u>