





3D View



(For Reference Only)
Stated At Compression

NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES


4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS


6-1: TERMINAL TO EAT FULL TIN, NOT PEELING, WELDING OBVIOUS COLOR AND OTHER ADVERSE

6-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT



TOLERANCE: ±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08


TOLERANCE: ±0.05MM
(FOR REFERENCE ONLY)

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
	DRAWN BY					
	LUDAH					
	CHEVKED BY					
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	/		TITLE: 天线弹片 L3.40*W1.00*H1.50		MANUFACTURE DWG	
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		PART NO. TP-T0-1521		SCALE	SHEET
					N:A	1:2
		LUJIAH				




Customer To Use Direction

Pull Out Direction
(出料方向)




The Carrier Tape Is Cold-Sealed
And The Peeling Angle Of The
Cold-Sealing Cover Tape Is 165°~180°.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密	
	DRAWN BY				
	LUDAH				
	CHEVKED BY				
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	/		TITLE: 天线薄片 L3.40*W1.00*H1.50		MANUFACTURE DWG
	DRAFT WHERE APPLICABLE APPROVED BY		PART NO. TP-T0-1521		
	MUST REMAIN WITHIN DIMENSIONS				
	LUJIAH		SCALE N:A		SHEET 2:2