








A



B



(For Reference Only)
Stated At Compression



3D View

NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.12MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H




5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS

C





METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)


GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密			
	DRAWN BY						
	LUDAH						
	CHEVKED BY						
DISTANCE ANGLE		/		TITLE: 天线弹片		MANUFACTURE DWG	
X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°		PART NO.		SCALE			
DRAFT WHERE APPLICABLE APPROVED BY		LUJIAH		TP-T1-4321		N:A	
MUST REMAIN WITHIN DIMENSIONS						SHEET	
						1:2	

D




Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
DISTANCE ANGLE	DRAWN BY				
X. ±0.30 X.* ±2.0°	LUDAH		TITLE: 天线薄片 L3.85*W1.60*H4.40		
.X ±0.20 .X* ±1.0°	CHEVKED BY				
.XX ±0.15 .XX* ±0.5°	/		MANUFACTURE DWG		
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS					
	LUJIAH		PART NO. TP-T1-4321		
			SCALE N:A		
			SHEET 2:2		