

Specification Sheet

Part Number: 151-02189



Integrated design allows for easy insertion by hand.

1.5–2mm panel thickness range allows for multiple applications.

Double-compression design that accommodates various sizes of wire and cable.

Presents a high extraction force for withstanding extreme conditions.

Low Profile 90° Metal Edge Clip, 1.5–2.0mm Panel Thickness, 6–6.2mm Cable Range, SS304, 100/bg

Article Number	151-02189
----------------	-----------

Type	MSC90
------	-------

Color	Metal (ML)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's 90-Degree Metal Edge Clip provides an excellent alternative to managing wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, this edge clip also has a high extraction force. The 90-degree configuration secures cables to a panel in a perpendicular orientation. Metal construction tolerates extreme environments, and a low-profile design allows the clip to be installed on a wide variety of module edges.
---------------------	---

Short Description	Low Profile 90° Metal Edge Clip, 1.5–2.0mm Panel Thickness, 6–6.2mm Cable Range, SS304, 100/bg
-------------------	--

Global Part Name	MSC90-SS304-ML
------------------	----------------

Length L (Imperial)	0.73
---------------------	------

Length L (Metric)	18.44
-------------------	-------

Fixation Method	Edge Clip
-----------------	-----------

Width W (Imperial)	0.460
--------------------	-------

Width W (Metric)	11.57
------------------	-------

Bundle Diameter Min (Imperial)	0.161
--------------------------------	-------

Bundle Diameter Min (Metric)	4.1
------------------------------	-----

Bundle Diameter Max (Imperial)	0.276
--------------------------------	-------

Bundle Diameter Max (Metric)	7.0
------------------------------	-----

Depth D (Imperial)	0.445
--------------------	-------

Depth D (Metric)	11.303
------------------	--------

Panel Thickness Min (Imperial)	0.06
--------------------------------	------

Panel Thickness Max (Imperial)	0.08
--------------------------------	------

Panel Thickness Min (Metric)	1.5
------------------------------	-----

Panel Thickness Max (Metric)	2.0
------------------------------	-----

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)