

MESSRS.**SPECIFICATION FOR APPROVAL****承 認 书**

Product	DYNAMIC SPEAKER
Part No.	HDK-3608BB-6C2 (RoHS)
Customer	
Customer Part No.	

Approved By	Checked By	Made By
王台平 JAN-06-2018	曹丽萍 JAN-06-2018	LILY JAN-06-2018

常 州 华 龙 电 子 有 限 公 司**DRAGONSTATE ELECTRONIC CORPORATION**

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

1.Specification

HDK-3608BB-6C2 (RoHS)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 36 mm	
03	Rated Input Power	1.0W	
04	Max. Input Power	1.5W for 1 minute	
05	Impedance	8 ohm $\pm$ 15% at 1500Hz.	
06	Resonance Frequency (Fo)	550Hz $\pm$ 20% at Fo, 1V	
07	Sensitivity (S.P.L.)	97dB (1.0W / 0.1m) $\pm$ 3 dB	at AVE0.6K,0.8K,1.0K,1.2KHz.
08	Frequency Range	Fo – 10KHz	
09	Total Harmonics Distortion	Max 8 % at 1 KHz,1.0W.	
10	Voice Coil	Diameter 13.3 mm	
11	Magnet	Rare earth permanent (Nd-Fe-B) magnet Φ 12.5*2.0 mm	
12	Weight	9.0g $\pm$ 0.2g	
13	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
14	Operation Test	Must be normal at program source – 1.0W	
15	Buzz, Rattle, etc.	Should not be audible at 2.83V sine Wave between Fo to 20KHz	
16	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
17	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
18	Temperature	Operating temperature: -20℃ to +60℃ Storage temperature: -30℃ to +70℃	

2. Test Condition

2.1 STANDARD

Temperature : 15 ~ 35℃

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

BASIC

Temperature : 20±3℃

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

2.2 Standard Test Fixture


1. Input Power : 1.0W (2.83V)

2. Zero Level : -dB

3. Mode : SPEAKER


4. potentiometer Range : 50dB

5. Sweep Time : 0.5sec



2.3 Frequency Response Curve


X:1.2500kHz *Y:97.11dB ZA:Live Curve SSR Fund.




Mode: SPEAKER



3.Dimension






4. Reliability test

Items.		Specifications
01	High temp. Test	Keep 96 hours at $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+60^{\circ}\text{C} \pm 3^{\circ}\text{C}$ relative humidity 95% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of; 
05	Thermal cycle test.	Low temperature: $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$, temperature: $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$, cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times.
09	Rated Power test	Rated Power white noise is applied for 96 hours
10	Max Power test	Max power 1 min on – 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.
Criterion: After these test , the change of S.P.L shall be within ± 3 dB .		

SOLDERING CONDITION

Recommend using constant branding iron in **15 ~ 30W**, and in temperature range **$350 \pm 10^{\circ}\text{C}$** .
 Soldering time not over **3** seconds.

5.Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
	 Cover{375*275*12mm} Material:Eps		
	 Box{375*275*48mm} 160pcs Material:Eps		
	 Middle{375*275*260mm} 800pcs(5*160pcs) Material:Eps		
	 Outer Box{570*390*260mm} 1600pcs(2*800pcs) Material: Paper		
单位：mm			
TITLE: packing		DRAWN: Lily DESIGNED: R&D OF D.S. CHECKED: Emily APPROVAL: Eric MATERIAL: ***	
PART NO.	1	SCALE: 2:1 SHEET: 1 of 1 UNITS: mm TOLERANCE	
DWG NO.		30~11 10~5 <4	± 0.3 ± 0.2 ± 0.1
DS		Changzhou Dragon State Electronic Co., Ltd	