







SPECIFICATIONS

Current Rating:0.75 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PH1.0-01-01PZD	1	0.00	1.0
PH1.0-01-02PZD	2	1.0	2.00
PH1.0-01-03PZD	3	2.00	3.00
PH1.0-01-04PZD	4	3.00	4.00
PH1.0-01-05PZD	5	4.00	5.00
PH1.0-01-06PZD	6	5.00	6.00
PH1.0-01-07PZD	7	6.00	7.00
PH1.0-01-08PZD	8	7.00	8.00
PH1.0-01-09PZD	9	8.00	9.00
.....			
PH1.0-01-50PZD	50	(PIN-1)	(PIN)

PART NUMBER DESCRIPTION:

PH1.0-01-NPZD

(D=单排;S=双排)

(Z=直脚;W=弯脚)

(PIN数量;01.....50PIN)

(排针开关)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:1.0PH H1.0 1xnPin 180° W1.5 PC2.0 PA2.0 PB1.0 L5.0 6T
			PAR PH1.0-01-NPZD
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X°±1'		APVD
X.XX±0.10	X.XX°±0.5'		SCALE N:A
CUSTOMER COPY		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A