








P.C.B LAYOUT
TOLERANCE:±0.05



Ordering Information: A1002WR-S-XP-LCP - ***

- 1.Part NO.
- 2.Finish:
(Blank): Tin over Nickel
G: Gold over Nickel



SPECIFICATIONS:

Current Rating: 1A AC,DC
Voltage Rating: 50V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 20mΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 500V AC/minute
Pin Material: Phosphor Bronze/Tin over Nickel
Solder Tabs: Phosphor Bronze/Tin over Nickel
Material: LCP,UL94V-0(Beige)

Ordering Information & Dimensions

Part NO.	Dimensions(mm)		
	A	B	C
A1002WR-S-2P-LCP	1.00	4.00	2.55
A1002WR-S-3P-LCP	2.00	5.00	3.55
A1002WR-S-4P-LCP	3.00	6.00	4.55
A1002WR-S-5P-LCP	4.00	7.00	5.55
A1002WR-S-6P-LCP	5.00	8.00	6.55
A1002WR-S-7P-LCP	6.00	9.00	7.55
A1002WR-S-8P-LCP	7.00	10.00	8.55
A1002WR-S-9P-LCP	8.00	11.00	9.55
A1002WR-S-10P-LCP	9.00	12.00	10.55
A1002WR-S-11P-LCP	10.00	13.00	11.55
A1002WR-S-12P-LCP	11.00	14.00	12.55
A1002WR-S-13P-LCP	12.00	15.00	13.55
A1002WR-S-14P-LCP	13.00	16.00	14.55
A1002WR-S-15P-LCP	14.00	17.00	15.55
A1002WR-S-16P-LCP	15.00	18.00	16.55
A1002WR-S-17P-LCP	16.00	19.00	17.55
A1002WR-S-18P-LCP	17.00	20.00	18.55
A1002WR-S-19P-LCP	18.00	21.00	19.55
A1002WR-S-20P-LCP	19.00	22.00	20.55

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet	TITLE	
mm	6:1	1 of 1		
DRWN	CHK'D	APPR	1.00mm PITCH RIGHT ANGLE WAFER -SMD TYPE	
Dengchun Yi	Diankui Wan	Jack Yin		
General Tolerances			THIRD ANGLE PROJECTION	DRAWING NO.
x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°				A1002WR-S-XP-LCP
REV			REV A2	

A2	MODIFY DRAWING	2021.10.28
A1	CHANGE THE DRAW NO.&INFORMATION	2019.05.23
A0	NEW RELEASE	2005.05.10
REV	DESCRIPTION	DATE