

Part Number : 2149201215

Series Number : 214920

Product Category : Power and Signal Cable Assemblies

Product Description : Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 450.00mm Length, 26 AWG, Black

Status : Active

## Documents & Resources

### Drawings

Drawing 2149201215\_sd.pdf

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

## General

Status	Active
Category	Power and Signal Cable Assemblies
Series	214920
Description	Pre-Crimped Lead PicoBlade Female-to-PicoBlade Female, Tin (Sn) Plating, 450.00mm Length, 26 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade Crimp Terminals
Keyword	Pre-Crimped Leads
Product Family	Off-the-Shelf Pre-Crimped Leads
Product Name	PicoBlade
UPC	193264502424

## Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

## Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.060/g
Packaging Type	Bag
Plating min - Mating	0.889µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Insulation Diameter	1.04mm max.

Wire Size (AWG)	26
-----------------	----

---

## Use with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>

---

This document was generated on Jul 19, 2024