

3D View

NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C




3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50μ" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)





METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




(For Reference Only)
Stated At Compression

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
	DRAWN BY			TITLE: 天线薄片 L2.50*W1.00*H1.85	MANUFACTURE DWG	
	LUDAH					
	CHEVKED BY			PART NO. TP-T0-1821	SCALE N:A	SHEET 1:2
/						
DISTANCE ANGLE						
X. ±0.30 X.* ±2.0°						
.X ±0.20 .X* ±1.0°						
.XX ±0.15 .XX* ±0.5°						
DRAFT WHERE APPLICABLE APPROVED BY						
MUST REMAIN						
WITHIN DIMENSIONS		LUJIAH				




Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	DRAWN BY		TITLE: 天线排片 L2.50*W1.00*H1.85			
	LUDAH					
	CHECKED BY		MANUFACTURE DWG			
	/					
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			PART NO. TP-T0-1821		SCALE	SHEET
	LUJIAH				N:A	2:2