





3D View

NOTES


- (1) MATERIAL: SUS-301 THICKNE=0.08mm
- (2) PRODUCT SPECIFICATIONS:
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 1.50V
 - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4: WELDING THRUST: ≥3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6: DURABILITY: 1500 CYCLES
- (3) SALT SPRAY: 24 HOURS
- (4) REQUIREMENTS
 - 4-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 4-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS



STATED AT COMPRESSION
(FOR REFERENCE ONLY)






RECOMMENDED PCB LAYOUT
TOLERANCE ±0.05 (角公差)



METAL MASK T=0.10
TOLERANCE ±0.05 (角公差)




GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	DRAWN BY LUDAH				
	CHECKED BY /		MANUFACTURE DWG		
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS				
	LUJIAH		SCALE SHEET N:A 1:2		




Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
	DRAWN BY LUDAH					
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	CHECKED BY /		TITLE: 天线弹片		MANUFACTURE DWG	
			ANTENNA SPRING,SMT T=0.08mm			
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			PART NO. TP-T1-3711		SCALE	SHEET
	LUJIAH				N:A	2:2