

3D View

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.08MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C




3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS, REACH, HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



(For Reference Only)
Stated At Compression



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密					
	DRAWN BY							
	LUDAH		TITLE: 天线薄片 L2.10*W1.00*H1.35		MANUFACTURE DWG			
	CHEVKED BY							
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°		/		PART NO. TP-T1-1311				
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		LUJIAH					SCALE N:A	
							SHEET 1:2	

A

B

C



D

A

B

C


D




Customer To Use Direction

Pull Out Direction

(出料方向)




The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is $165^{\circ} \sim 180^{\circ}$ And The Peeling Force Is $30 \sim 120g$.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES
(UNLESS SOECIFIED)

SCALE: 1:1
UNIT: MM



瑾珩精密

DISTANCE ANGLE
X. ± 0.30 X.* $\pm 2.0^{\circ}$
.X ± 0.20 .X* $\pm 1.0^{\circ}$
.XX ± 0.15 .XX* $\pm 0.5^{\circ}$

DRAWN BY
LUDAH
CHECKED BY
/

TITLE: 天线晶片
L2.10*W1.00*H1.35

MANUFACTURE DWG

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

LUJIAH

PART NO.
TP-T1-1311

SCALE
N:A

SHEET
2:2