







3D View

NOTES

- (1) MATERIAL: SUS-301 THICKNE=0.15mm
- (2) PRODUCT SPECIFICATIONS:
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 1.50V
 - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4: WELDING THRUST: ≥ 3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6: DURABILITY: 1500 CYCLES
- (3): SALT SPRAY: 24 HOURS
- (4): FINISH: 50u"Min NICKEL UNDERPLATING OVER ALL.
- (5): REQUIREMENTS
 - 5-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS




RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05




SOLDER AREA



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	DRAWN BY	TITLE: 天线弹片 H1.65 WIRE CLAMP,SMT T=0.15mm			
	LUDAH				
	CHEVKED BY	MANUFACTURE DWG			
	/				
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		PART NO.	SCALE	SHEET	
	LUJIAH	XJ-T2-1611	N:A	1:2	



CONN. QTY./REEL	REEL QTY./CARTON	CONN. QTY./CARTON
3500	20	70,000



← PRODUCT PACKAGING DIRECTION
CUSTOMER TO USE DIRECTION →



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密	
DISTANCE ANGLE X. ±0.30 X.* ±2.0* .X ±0.20 .X* ±1.0* .XX ±0.15 .XX* ±0.5*	DRAWN BY		TITLE: 天线弹片 H1.65 WIRE CLAMP,SMT T=0.15mm	
	LUDAH			
	CHEVKED BY		MANUFACTURE DWG	
/				
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			PART NO.	
	LUJIAH		XJ-T2-1611	
			SCALE	SHEET
			N:A	2:2