





RoHS





2P (外观)

3P (外观)



4P~20P (外观随孔位递进自然变化)




Curved needle length	
Code	L
C15	1.5
C22	2.2

Model No.	Pin	A	B	C
WAFER-MX1.25-2PWZ-C□□-9T	2	1.25	4.45	3.20
WAFER-MX1.25-3PWZ-C□□-9T	3	2.50	5.70	4.45
WAFER-MX1.25-4PWZ-C□□-9T	4	3.75	6.95	5.70
WAFER-MX1.25-5PWZ-C□□-9T	5	5.00	8.20	6.95
WAFER-MX1.25-6PWZ-C□□-9T	6	6.25	9.45	8.20
WAFER-MX1.25-7PWZ-C□□-9T	7	7.50	10.70	9.45
WAFER-MX1.25-8PWZ-C□□-9T	8	8.75	11.85	10.70
WAFER-MX1.25-9PWZ-C□□-9T	9	10.00	13.20	11.85
WAFER-MX1.25-10PWZ-C□□-9T	10	11.25	14.35	13.20
WAFER-MX1.25-11PWZ-C□□-9T	11	12.50	15.70	14.35
WAFER-MX1.25-12PWZ-C□□-9T	12	13.75	16.95	15.70
WAFER-MX1.25-13PWZ-C□□-9T	13	15.00	18.20	16.95
WAFER-MX1.25-14PWZ-C□□-9T	14	16.25	19.45	18.20
WAFER-MX1.25-15PWZ-C□□-9T	15	17.50	20.70	19.45
WAFER-MX1.25-16PWZ-C□□-9T	16	18.75	21.95	20.70
WAFER-MX1.25-17PWZ-C□□-9T	17	20.00	23.20	21.95
WAFER-MX1.25-18PWZ-C□□-9T	18	21.25	24.45	23.20
WAFER-MX1.25-19PWZ-C□□-9T	19	22.50	25.70	24.45
WAFER-MX1.25-20PWZ-C□□-9T	20	23.75	26.95	25.70

Specifications/技术规格:

- 1.Poles/线数: 2~20P
- 2.Wire range/适用线规: AGW 32#~28#
- 3.Applicable PC board thickness/适用PC板厚度: 0.6~1.2mm
- 4.Current rating/额定电流: 1.0A
- 5.Voltage rating/额定电压: 125V DC/AC
- 6.Insulation Resistance/绝缘电阻: 100MΩ Min
- 7.Dielectric Withstanding/ 耐电压: 500V AC/minute
- 8.Contact Resistance/ 接触电阻: 20mΩ Max
- 9.Operating Temperature/ 工作温度: -25℃ to +85℃



适用线路板 (PCB LAYOUT)

Ⓑ	Terminal			Brass	Plating Sn
Ⓐ	Housing		1	PA9T	Off White
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co, Ltd

design	date	name	WAFER CONNECTOR
Review	date	model	WAFER-MX1.25-□□PWZ-C□□-9T
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

angle	±2'
10~30	±0.30
5~10	±0.20
~ 5	±0.10

modify Review Approved Tolerance not specified