










3D View

NOTES


- (1) MATERIAL: SUS-304 THICKNE=0.10mm
- (2) PRODUCT SPECIFICATIONS:
 - 2-1: RATED CURRENT: 1.0A
 - 2-2: VOLTAGE RATING: 1.50V
 - 2-3: CONTACT RESISTANCE: 80mΩ/MAX
 - 2-4: WELDING THRUST: >3KG
 - 2-5: OPERATING TEMPERATURE: -40°C~+85°C
 - 2-6: DURABILITY: 1500 CYCLES
- (3) SALT SPRAY: 24 HOURS
- (4) REQUIREMENTS
 - 4-1: TERMINAL TO EAT FULL TIN, NOT PEELING WELDING OBVIOUS COLOR AND OTHER ADVERSE
 - 4-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS




GENERAL TOLERANCES (UNLESS SOECIFIED)		SCALE: 1:1 UNIT: MM		 瑾珩精密	
DISTANCE ANGLE		DRAWN BY			
X. ±0.30	X.* ±2.0°	LUDAH		TITLE: 天线薄片	
.X ±0.20	.X* ±1.0°	CHEVKED BY			
.XX ±0.15	.XX* ±0.5°	/		MANUFACTURE DWG	
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		LUJIAH			
				PART NO. TP-T0-3521	
				SCALE N:A	
				SHEET 1:2	



Customer To Use Direction Pull Out Direction (出料方向)



The Carrier Tape Is Cold-Sealed And The Peeling Angle Of The Cold-Sealing Cover Tape Is 165°~180°.



Carton Size 290*330*4 K3K

Carton Size 345*345*360 K=K

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密		
	DRAWN BY LUDAH					
	CHEVKED BY /		TITLE: 天线弹片 H3.55 ANTENNA SPRING, SMT T=0.10mm		MANUFACTURE DWG	
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		PART NO. TP-T0-3521		SCALE N:A	SHEET 2:2