


■ Features

- High Voltage : $V_{CE0} = -120V$
- High Transition Frequency : $f_T = 120MHz(typ.)$
- Small Flat Package
- Complementary to 2SC2881


SOT-89

1.BASE

2.COLLECTOR

3.EMITTER

■ Absolute Maximum Ratings $T_a = 25^{\circ}C$

Parameter	Symbol	Rating	Unit
Collector-Emitter Voltage	V_{CE0}	-120	V
Collector-Base Voltage	V_{CB0}	-120	V
Emitter-Base Voltage	V_{EB0}	-5	V
Collector Current	I_C	-800	mA
Base Current	I_B	-160	mA
Collector Power Dissipation	P_C	500	mW
Jumction temperature	T_j	150	$^{\circ}C$
Storage temperature	T_{stg}	-55 to +150	$^{\circ}C$


■ Electrical Characteristics $T_a = 25^{\circ}C$

Parameter	Symbol	Testconditons	Min	Typ	Max	Unit
Emitter Cut-off Current	I_{E0}	$V_{EB} = -5V, I_C = 0$			-0.1	μA
Collector Cut-off Current	I_{C0}	$V_{CB} = -120V, I_E = 0$			-0.1	μA
Collector-Emitter Breakdown Voltage	$V_{(BR)CE0}$	$I_C = -10mA, I_B = 0$	-120			V
Emitter-Base Breakdown Voltage	$V_{(BR)EB0}$	$I_E = -1mA, I_C = 0$	-5			V
DC Current Gain	h_{FE}	$V_{CE} = -5V, I_C = -100mA$	80		240	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = -500mA, I_B = -50mA$			-1.0	V
Base-Emitter Voltage	V_{BE}	$V_{CE} = -5V, I_C = -500mA$			-1.0	V
Transtion Frequency	f_T	$V_{CE} = -5V, I_C = -100mA$		120		MHz
Collector Output Capacitance	C_{ob}	$V_{CB} = -10V, I_E = 0, f = 1MHz$			30	pF

■ hFE Classification


Rank	O	Y
hFE	80~160	120~240

■ Electrical Characteristics Curves



Package Information

SOT-89



SYMBOL	mm	
	min	max
A	1.40	1.60
b1	0.35	0.50
b2	0.45	0.60
c	0.36	0.46
D	4.30	4.70
D1	1.40	1.80
E	4.00	4.40
E1	2.30	2.70
e	1.50BSC	
L	0.80	1.20