




3D View



NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES



4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING, WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




(For Reference Only)
Stated At Compression




RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)





METAL MASK T=0.08



TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
	DISTANCE ANGLE X. ±0.30 X.* ±2.0* .X ±0.20 .X* ±1.0* .XX ±0.15 .XX* ±0.5*	DRAWN BY		TITLE: 天线弹片 L2.80*W1.50*H1.10		MANUFACTURE DWG
		LUDAH				
		CHEVKED BY				
	/	PART NO. TP-T1-1121		SCALE N:A	SHEET 1:2	
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS	LUJIAH					



The Carrier Tape Is Heat-Sealed
Packaging The Peeling Angle Of The
Heat-Sealing Cover Tape Is 165°~180°
And The Peeling Force Is 30~120g.



20Reel

Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K

Label

GENERAL TOLERANCES
(UNLESS SOECIFIED)

SCALE: 1:1
UNIT: MM

DISTANCE ANGLE
X. ±0.30 X.* ±2.0°
.X ±0.20 .X* ±1.0°
.XX ±0.15 .XX* ±0.5°

DRAWN BY
LUDAH
CHECKED BY
/

DRAFT WHERE APPLICABLE APPROVED BY
MUST REMAIN
WITHIN DIMENSIONS

LUJIAH



瑾珩精密

TITLE: 天线排片
L2.80*W1.50*H1.10

PART NO.
TP-T1-1121

MANUFACTURE DWG

SCALE
N:A

SHEET
2:2