


NOTES

(1) MATERIAL: SUS-304 THICKNESS=0.10mm

(2) PRODUCT SPECIFICATIONS:

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.50V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

2-6: DURABILITY: 1500 CYCLES

(3): SALT SPRAY: 24 HOURS






(4): FINISH: 50u"Min NICKEL UNDERPLATING OVER ALL.

(5): REQUIREMENTS

5-1: TERMINAL TO EAT FULL TIN, NOT PEELING



WELDING OBVIOUS COLOR AND OTHER ADVERSE

5-2: ROHS, REACH, HF HALOGEN ADVERSE OF DOMESTIC AND INTERNATIONAL ENVIRONMENTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT


GENERAL TOLERANCE ±0.05




GENERAL TOLERANCES (UNLESS SOECIFIED)		SCALE: 1:1 UNIT: MM		 瑾珩精密							
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X.* ±1.0° .XX ±0.15 .XX.* ±0.5°		DRAWN BY LUDAH					TITLE: 天线弹片 H1.10 ANTENNA SPRING TERMINAL,T=0.10mm		MANUFACTURE DWG		
		CHECKED BY /									
		DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		/		PART NO. TP-T0-1111		SCALE		SHEET	
				LUJIAH				N:A		1:2	



← PRODUCT PACKAGING DIRECTION
CUSTOMER TO USE DIRECTION →



TOTAL
20LAYERS



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM	 瑾珩精密	
DISTANCE ANGLE	DRAWN BY	TITLE: 天线弹片 H1.10 ANTENNA SPRING TERMINAL,T=0.10mm	
X. ±0.30 X.* ±2.0°	LUDAH		
.X ±0.20 .X* ±1.0°	CHEVKED BY		
.XX ±0.15 .XX* ±0.5°	/		
DRAFT WHERE APPLICABLE APPROVED BY		PART NO. TP-T0-1111	MANUFACTURE DWG
MUST REMAIN WITHIN DIMENSIONS	LUJIAH		SCALE N:A