


(For Reference Only)
Stated At Compression



NOTES:

1:MATERIAL

1-1: C5191 THICKNE=0.15MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES




4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS





3D View





RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM (FOR REFERENCE ONLY)




GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
	DRAWN BY			TITLE: 天线薄片 L4.00*W1.50*H2.55	MANUFACTURE DWG	
	LUDAH					
	CHEVKED BY					
DISTANCE ANGLE X. ±0.30 X* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	/		PART NO. TP-T0-2531	SCALE	SHEET	
	LUJIAH			N:A	1:2	
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS					




Customer To Use Direction

Pull Out Direction
(出料方向)





The Carrier Tape Is Cold-Sealed
And The Peeling Angle Of The
Cold-Sealing Cover Tape Is 165°~180°.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密			
DISTANCE ANGLE	DRAWN BY					
X. ±0.30 X.* ±2.0°	LUDAH		TITLE: 天线晶片 L4.00*W1.50*H2.55		MANUFACTURE DWG	
.X ±0.20 .X* ±1.0°	CHEVKED BY					
.XX ±0.15 .XX* ±0.5°	/					
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS			PART NO. TP-T0-2531		SCALE	SHEET
	LUJIAH				N:A	2:2