

3D View

NOTES:

1:MATERIAL

1-1: SUS-304 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C





3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,  
WELDING OBVIOUS COLOR AND OTHED ADVERSE  
6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC  
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM  
(FOR REFERENCE ONLY)

METAL MASK T=0.08

TOLERANCE:±0.05MM  
(FOR REFERENCE ONLY)



(For Reference Only)  
Stated At Compression

|                                                                                             |                        |        |                                                                                       |                                  |  |                 |  |       |  |
|---------------------------------------------------------------------------------------------|------------------------|--------|---------------------------------------------------------------------------------------|----------------------------------|--|-----------------|--|-------|--|
| GENERAL TOLERANCES<br>(UNLESS SOECIFIED)                                                    | SCALE: 1:1<br>UNIT: MM |        |  | 瑾珩精密                             |  |                 |  |       |  |
|                                                                                             | DRAWN BY               |        |                                                                                       |                                  |  |                 |  |       |  |
|                                                                                             | LUDAH                  |        |                                                                                       |                                  |  |                 |  |       |  |
|                                                                                             | CHEVKED BY             |        |                                                                                       |                                  |  |                 |  |       |  |
| DISTANCE ANGLE<br>X. ±0.30    X.* ±2.0*<br>.X ±0.20    .X* ±1.0*<br>.XX ±0.15    .XX* ±0.5* |                        | /      |                                                                                       | TITLE: 天线弹片<br>L2.90*W1.00*H1.40 |  | MANUFACTURE DWG |  |       |  |
| DRAFT WHERE APPLICABLE APPROVED BY<br>MUST REMAIN<br>WITHIN DIMENSIONS                      |                        |        |                                                                                       | PART NO.<br>TP-T1-1421           |  | SCALE           |  | SHEET |  |
|                                                                                             |                        | LUJIAH |                                                                                       |                                  |  | N:A             |  | 1:2   |  |

