




3D View



(For Reference Only)
Stated At Compression

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C


3:DURABILITY: 1500 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN


6:REQUIREMENTS

6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE
6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS



RECOMMENDED PCB LAYOUT



TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)




METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)


GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密						
	DRAWN BY								
	LUDAH		TITLE: 天线薄片 L3.15*W1.00*H1.50		MANUFACTURE DWG				
	CHEVKED BY								
DISTANCE ANGLE		/		PART NO. TP-T1-1551		SCALE		SHEET	
X. ±0.30 X.* ±2.0°						N:A		1:2	
.X ±0.20 .X* ±1.0°									
.XX ±0.15 .XX* ±0.5°									
DRAFT WHERE APPLICABLE APPROVED BY		LUJIAH							
MUST REMAIN									
WITHIN DIMENSIONS									



Customer To Use Direction Pull Out Direction (出料方向)





The Carrier Tape Is Heat-Sealed Packaging The Peeling Angle Of The Heat-Sealing Cover Tape Is 165°~180° And The Peeling Force Is 30~120g.



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM			瑾珩精密	
	DRAWN BY				
	LUDAH				
	CHEVKED BY				
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	/		TITLE: 天线排片 L3.15*W1.00*H1.50		MANUFACTURE DWG
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		PART NO. TP-T1-1551		
	LUJIAH		SCALE N:A		SHEET 2:2