

1456488

https://www.phoenixcontact.com/pc/products/1456488

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M12-SPEEDCON, coding: B, Rear mounting, Pg9, Solder pins, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239813

Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- · All standard pin assignments and codings for signal, data, and power transmission with a uniform design-in design
- · For high transmission reliability: optional shield connection to the housing by means of shield contact

Commercial data

Item number	1456488
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ABQEHB
Catalog page	Page 62 (PC-2011)
GTIN	4046356617222
Weight per piece (including packing)	14.61 g
Weight per piece (excluding packing)	14.5 g
Customs tariff number	85366990
Country of origin	DE



1456488

https://www.phoenixcontact.com/pc/products/1456488

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	Lock nut is included in the scope of delivery

Mounting

Mounting type	Rear mounting Pg9 With flat nut
Assembly note	With flat nut

Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	В
Thread type	M12
Insulation characteristics	

П

3

Dimensions

Length of the solder pin	6 mm
	6 mm

Material specifications

Overvoltage category

Degree of pollution

Flammability rating according to UL 94	V0
Seal material	NBR
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	60 V
Nominal current I _N	4 A



1456488

https://www.phoenixcontact.com/pc/products/1456488

Connection data

Conductor connection

Connection method	Solder pins
Contact connection type	Socket

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON
Coding	В

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)

Standards and regulations

M12


Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101



1456488

https://www.phoenixcontact.com/pc/products/1456488

Drawings



Pin assignment M12 socket, 5-pos., B-coded, female side



1456488

https://www.phoenixcontact.com/pc/products/1456488

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/pc/products/1456488

c 911 us	cULus Recogniz Approval ID: E221474	zed 4-20140616			
		Nominal voltage U_N	Nominal current I _N	Cross section AWG	Cross section mm ²
		60 V	4 A	-	-

71	UL Recognized Approval ID: E118976-20100522						
		Nominal voltage U_N	Nominal current I _N	Cross section AWG	Cross section mm ²		
		60 V	4 A	22 - 22	-		



1456488

https://www.phoenixcontact.com/pc/products/1456488

Classifications

ECLASS

	ECLASS-11.0	27440102		
	ECLASS-12.0	27440116		
	ECLASS-13.0	27440116		
ET	ETIM			
	ETIM 9.0	EC002635		
UN	ISPSC			

U



1456488

https://www.phoenixcontact.com/pc/products/1456488

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes		
Exemption	6(c)		
China RoHS			
Environment friendly use period (EFUP)	EFUP-50		
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.		
EU REACH SVHC			
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)		
SCIP	e7bc41d0-bd15-43a0-8fb4-df3183517a85		

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG Flachsmarktstraße 8 D-32825 Blomberg +49 (0) 5235-3 00 info@phoenixcontact.com