



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Blade Receptacle**  
Mating Tab Width: **.51 mm [ .02 in ]**  
Mating Tab Thickness: **.51 mm [ .02 in ]**  
Magnet Wire Size: **.16 – 1.02 mm**

Features

Product Type Features

|                                    |                    |
|------------------------------------|--------------------|
| Compatible With Discrete Wire Type | Magnet Wire, Solid |
|------------------------------------|--------------------|

Contact Features

|                           |                  |
|---------------------------|------------------|
| Magnet Wire Terminal Type | Blade Receptacle |
| Mating Tab Width          | .51 mm[.02 in]   |
| Mating Tab Thickness      | .51 mm[.02 in]   |
| Terminal Plating Material | Unplated         |
| Terminal Orientation      | Straight         |

Termination Features

|                                    |                               |
|------------------------------------|-------------------------------|
| Termination Method to Wire & Cable | Insulation Displacement (IDC) |
|------------------------------------|-------------------------------|

Mechanical Attachment

|                       |       |
|-----------------------|-------|
| Mating Retention Type | Barbs |
|-----------------------|-------|

Dimensions

|                  |                |
|------------------|----------------|
| Terminal Height  | 7.62 mm[.3 in] |
| Magnet Wire Size | .16 – 1.02 mm  |



|                                    |                |
|------------------------------------|----------------|
| Stock Thickness (Magnet Wire Side) | .51 mm[.02 in] |
|------------------------------------|----------------|

|                |                |
|----------------|----------------|
| Product Length | 7.62 mm[.3 in] |
|----------------|----------------|

Usage Conditions

|                   |             |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -40 – 125 °C[-40 – 257 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                                    |        |
|------------------------------------|--------|
| Compatible With Wire Base Material | Copper |
|------------------------------------|--------|

Packaging Features

|                  |      |
|------------------|------|
| Packaging Method | Reel |
|------------------|------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                              |           |
|------------------------------|-----------|
| EU RoHS Directive 2011/65/EU | Compliant |
|------------------------------|-----------|

|                             |           |
|-----------------------------|-----------|
| EU ELV Directive 2000/53/EC | Compliant |
|-----------------------------|-----------|

|                                               |                                         |
|-----------------------------------------------|-----------------------------------------|
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
|-----------------------------------------------|-----------------------------------------|

|                                        |                                                                                                                               |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2024 (240)<br>Candidate List Declared Against: JAN 2024 (240)<br>Does not contain REACH SVHC |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|

|                 |                                                                                     |
|-----------------|-------------------------------------------------------------------------------------|
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
|-----------------|-------------------------------------------------------------------------------------|

|                           |                                              |
|---------------------------|----------------------------------------------|
| Solder Process Capability | Not applicable for solder process capability |
|---------------------------|----------------------------------------------|

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1601095-2  
131-165-014=TAB,PCB,STD,SMZ

TE Part # 2-1601075-1  
WIRE2BLADE,STD, SMZ

TE Part # 1601075-1  
WIRE2BLADE,STD, SMZ

TE Part # 1601204-2  
.110 X .020 TAB STD SIAMEZE

TE Part # 1601045-1  
131-093-000=TAB,110X020,STD,SMZ

TE Part # 1601075-2  
131-145-014=WIRE2BLADE,STD,SMZ

TE Part # 2-1601045-1  
.110X.020 TAB,STD,SMZ

TE Part # 2-1601059-1  
131-126-000=TAB,110X020,STD,SMZ

TE Part # 2-1601196-1  
WIRE2BLADE,HIGH CARRIER,STD,SMZ

TE Part # 2310498-2  
STD,HIGH CARRIER WIRE TO BALDE SIAMEZE

TE Part # 2322343-2  
WIRE2WIRE,STD,SMZ FOR AL WIRE

TE Part # 2348500-2  
WIRE TO BLADE SMZ TERMINAL FOR AL WIRE

TE Part # 4-1601075-1  
WIRE2BLADE,STD,SMZ

TE Part # 1601196-2  
WIRE2BLADE,HIGH CARRIER,STD,SMZ

TE Part # 1601196-3  
WIRE2BLADE,HIGH CARRIER,STD,SMZ


Also in the Series | SIAMEZE

Insertion & Extraction Tools(1)

Magnet Wire Terminals(192)

Customers Also Bought





Documents

Product Drawings

WIRE2BLADE,HIGH CARRIER,STD,SMZ

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1601196-1\_B.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1601196-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1601196-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

1-1773702-7 \_IDC\_Magnet\_Wire

English

Product Specifications

Application Specification

English