


NOTES:

1:MATERIAL

1-1: TITANIUM COPPER THICKNE=0.10MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 1.5V

2-3: CONTACT RESISTANCE: 80mΩ/MAX

2-4: WELDING THRUST: ≥3KG

2-5: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 1500 CYCLES






4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS


6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS.REACH.HF HALOGER ADVERSE OF DOMESTIC
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS





RECOMMENDED PCB LAYOUT

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



METAL MASK T=0.08

TOLERANCE:±0.05MM
(FOR REFERENCE ONLY)



3D View

GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密						
	DRAWN BY								
	LUDAH		TITLE: 天线弹片 L3.50*W1.50*H2.03		MANUFACTURE DWG				
	CHEVKED BY								
DISTANCE ANGLE X. ± 0.30 X.* $\pm 2.0^{\circ}$.X ± 0.20 .X* $\pm 1.0^{\circ}$.XX ± 0.15 .XX* $\pm 0.5^{\circ}$		/		PART NO. TP-T0-2011		SCALE		SHEET	
DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS		LUJIAH				N:A		1:2	



瑾珩精密



TITLE: 天线弹片
L3.50*W1.50*H2.03

MANUFACTURE DWG

PART NO.
TP-T0-2011



SCALE
N:A

SHEET
1:2





Customer To Use Direction

Pull Out Direction
(出料方向)



Carton Size
290*330*4 K3K

Carton Size
345*345*360 K=K



GENERAL TOLERANCES (UNLESS SOECIFIED)	SCALE: 1:1 UNIT: MM		 瑾珩精密		
DISTANCE ANGLE X. ±0.30 X.* ±2.0° .X ±0.20 .X* ±1.0° .XX ±0.15 .XX* ±0.5°	DRAWN BY LUDAH				
	CHECKED BY /		MANUFACTURE DWG		
	DRAFT WHERE APPLICABLE APPROVED BY MUST REMAIN WITHIN DIMENSIONS				
	LUJIAH		SCALE N:A		
		SHEET 2:2			