




6A Glass Passivated Single-Phase Bridge Rectifier

特征/Features	外形尺寸/Outline Dimensions
◆ GPP芯片 Glass passivated chip ◆ 低反向漏电流 Low Reverse Leakage Current ◆ 高耐浪涌电流能力 High surge current capability ◆ 接线端与壳体间绝缘耐压2500V Case to Terminal Isolation Voltage 2500V	Case: GBL Series Dimensions in millimeters 
机械参数/Mechanical Data	
◆ 本体：塑封 Case: plastic package ◆ 标识/极性：本体标记 Marking / Polarity: Marked on Body ◆ 重量：约克 Weight: About 2.2 grams	

极限值/Maximum Ratings and Thermal Characteristics @ Ta = 25℃ unless otherwise noted

符号 Symbol	特性 Characteristic	GBL6							单位 Unit
		005	01	02	04	06	08	10	
V _{RRM}	最大反向重复峰值电压 Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
I _F (AV)	平均整流输出电流 Average Forward Output Rectified Current@Ta =85℃	6							A
V _F	正向峰值电压 Forward Voltage Per Leg @I _{FM} =6.0A	1.1							V
I _{FSM}	正向浪涌电流 Peak Forward Surge Current 8.3ms Single Half Sine-wave superimposed on rated load	200							A
I _R	反向漏电流 Maximum DC reverse current at rated Ta = 25℃ DC blocking voltage per leg Ta = 125℃	5 500							uA
i ² t	热容值 Rating for fusing (t<8.3ms)	166							A ² S
V _{isol}	绝缘耐压 Rms isolation voltage from case to leads	2500							V
R _{θJC}	热阻 Maximum thermal resistance per leg	4.2							℃/W
T _j , T _{STG}	结温， 存储条件 Operating Junction and storage temperature range	-55~150							℃

Note:
(1) Junction to case with heatsink
(2) Recommended mounting position is to bolt down on heatsink with silicone thermal compound for maximum heat transfer with M3 screw .



6A Glass Passivated Single-Phase Bridge Rectifier

■特性曲线（典型） Characteristics(Typical)

Fig 1-forwardCurrent derating Curve
图1正向电流降额曲线




Fig.2-Maximum Non-Repetitive Surge Current
图2最大不重复正向浪涌曲线




Fig.3-Typical Reverse Characteristics
图3.典型的反向特性




Fig.4-Typical Forward Characteristics
图4.典型的正向特性

