

MESSRS.

SPECIFICATION FOR APPROVAL**承 認 書**

Product	DYNAMIC SPEAKER
Part No.	HDK-4008BB-8C (RoHS)
Customer Approval	

Approved By	Checked By	Made By
王台平 JUL-07-2018	曹丽萍 JUL-07-2018	LILY JUL-07-2018

常 州 华 龙 电 子 有 限 公 司
Changzhou Dragon State Electronic Co., Ltd

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.1

1. Specification

HDK-4008BB-8C (RoHS)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 40 mm	
03	Rated Input Power	0.2W	
04	Max. Input Power	0.5W for 1 minute	
05	Impedance	8 ohm $\pm$ 15% at 1000Hz.	
06	Resonance Frequency (Fo)	400Hz $\pm$ 20% at Fo, 1V	
07	Sensitivity (S.P.L.)	92dB (0.2W / 0.1m) $\pm$ 2dB	at AVE 0.6,0.8,1.0,1.2 KHz
08	Frequency Range	Fo – 4.5KHz	
09	Total Harmonics Distortion	Max 8 % at 1 KHz,0.2W.	
10	Voice Coil	Diameter 13.3mm	
11	Magnet	Rare earth permanent (Nd-Fe-B) magnet Φ 12.5x1.5 mm	
12	Weight	10g $\pm$ 0.5g	
13	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
14	Operation Test	Must be normal at program source – 0.2W	
15	Buzz, Rattle, etc.	Should not be audible at 1.26V sine Wave between Fo to 5KHz	
16	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
17	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
18	Temperature	Operating temperature: -20°C to +60°C Storage temperature: -30°C to +70°C	

2-1. Test Condition

Standard

Temperature : 15 ~ 35℃

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

Basic

Temperature : 20±3℃

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

2-2. Standard Test Fixture


1. Input Power : 0.2W (1.26V)

2. Zero Level : -dB


3. Mode : SPEAKER

4. potentiometer Range : 50dB


5. Sweep Time : 0.5sec




2-3.Frequency Response Curve



3.Dimension



4. Reliability Tests




Items.		Specifications
01	High temp. Test	Keep 96 hours at $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+40^{\circ}\text{C} \pm 3^{\circ}\text{C}$ relative humidity 95% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of; 
05	Thermal cycle test.	Low temperature: $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$, temperature: $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$, cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times.
09	Rated Power test	Rated Power white noise is applied for 96 hours
10	Max Power test	Max power 1 min on – 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.
Criterion: After these test , the change of S.P.L shall be within ± 3 dB .		

Soldering Condition

Recommend using constant branding iron in **15 ~ 30W**, and in temperature range **$350 \pm 10^{\circ}\text{C}$** .

Soldering time not over **3** seconds.

5. Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
			
	Cover{375*275*12mm} Material:Eps		
	↓		
			
	Box{375*275*48mm} 200pcs Material:Eps		
			
	Middle{375*275*260mm} 1000pcs{5*200pcs} Material:Eps		
	↓		
			
	Outer Box{570*390*260mm} 2000pcs{2*1000pcs} Material: Paper		
单位：mm			
TITLE: packing		DRAWN: Lily 2013/12/06	
PART NO.		DESIGNED: R&D OF D.S.	
DWG NO.		CHECKED: Emily	
		APPROVAL: Eric	
		MATERIAL: ***	
1		SCALE: 1:1	
REV		SHEET: 1 of 1	
		UNITS: mm	
		TOLERANCE	
		20~11 ± 0.3	
		10~5 ± 0.2	
		<4 ± 0.1	
DS Changzhou Dragon State Electronic Co., Ltd			