





1

RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 1.0±0.10MM;DEFAULT TOLERANCE:±0.05

5

PIN	NUMBER	SIGNAL	NAME
A1		GND	
A2		SSTXp1	
A3		SSTXn1	
A4		Vbus	
A5		CC1	
A6		Dp1	
A7		Dn1	
A8		SBU1	
A9		Vbus	
A10		SSRXn2	
A11		SSRXp2	
A12		GND	
B12		GND	
B11		SSRXp1	
B10		SSRXn1	
B9		Vbus	
B8		SBU2	
B7		Dn2	
B6		Dp2	
B5		CC2	
B4		Vbus	
B3		SSTXn2	
B2		SSTXp2	
B1		GND	

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					
DIM. TOL. X ±0.30 X.X ±0.25 X.XX ±0.15 GENERAL ANGLE: ±3°		TITLE: <i>USB CF24P VERTICAL SMT</i>					
		DWG. NO.: <i>UC04-0B24F00P11</i>		DRAWN: MAX			
		PART NO.: <i>UC04-0B24F00P11</i>		CHECKED: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL