










A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL




SECTION A-A

4.2. Wetting Temperature: 265 ± 5 C, 5 ± 0.5 s



• • • • •



RECOMMENDED ^(TOP VIEW) P.C.B. LAYOUT (T:1.0~1.2mm)
TOLERANCE UNSPECIFIED ±0.05mm

WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A