




REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

Material declaration		
No	NAME	MATERIAL
①	1#接触端子	磷铜带 C5210R-EH(t=0.2mm) G/F
②	2#接触端子	磷铜带 C5210R-EH(t=0.2mm) G/F
③	3#接触端子	磷铜带 C5210R-EH(t=0.2mm) G/F
④	底座	PBT / Black
⑤	后盖	PBT / Black
⑥	螺帽	SUS304 不锈钢

PROJECT		LEVEL		A[better product]	B[average product]
Electrical Properties	Contact Rating		1.0A, 24V DC		
	Initial Contact Resistance		50mΩ max.		
	Insulation Resistance		100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC		
	Withstand Voltage		500V AC for 1 minute 350 V AC for 1 minut		
Durable Performance	There No Load		6,000 Cycles 5,000 Cycles		
	Rated Load		5,000 Cycles 4,000 Cycles		
Storage temp.			-35℃～+75℃(Operating Temp:		

DIMENSION CLASSIFICATION	
■	CRITICAL
☒	MAJOR

TOLERANCE TABLE	
.X	± 0.40
.XX	± 0.25
.XXX	± 0.10
ANGLE	± 2°

台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		TITLE PJ-392 立插式3.5耳机插座-帶螺帽-焊端帶孔		開關,連接器 SOFNG	
PART NO.	PJ-392	SERIES	SD106		
APPROVED	Peck	DWG NO.	SOF-G006		
CHECKED	Paul	SCALE	1:1	UNIT	mm
DRAWIN	David	REV	AO	SHEET NO.	1/1