


Features

- Low profile package
- Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- High forward surge capability
- Compliant with RoHS standards, halogen-free

Mechanical Data

- Package: SOD-123FL
- Terminals: Tin plated leads, solderable per
- Polarity: Cathode line denotes the cathode end



Maximum Ratings ($T_a=25^{\circ}\text{C}$ Unless otherwise specified)

Parameter	Symbol	SS24L	Unit
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	40	V
Maximum RMS Voltage	V_{RMS}	28	V
Maximum DC Blocking Voltage	V_{DC}	40	V
Maximum Average Forward Rectified current at T_L (See Fig.1)	$I_{F(AV)}$	2	A
Peak Forward Surge Current (8.3 ms single half sine-wave superimposed on rated load)	I_{FSM}	40	A
Operating Junction Temperature Range	T_J	- 55 to + 125	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	- 55 to + 125	$^{\circ}\text{C}$




Electrical Characteristics

Parameter	Test Conditions	Symbol	SS24L	Unit
Maximum Instantaneous Forward Voltage	$I_F=2A$	V_F	0.40	V
Maximum DC Reverse Current at Rated DC Blocking Voltage	$T_A=25^{\circ}C$	I_R	0.20	mA
Typical Junction Capacitance	4.0 V, 1 MHz	C_J	130	pF

Characteristics Curves


AVERAGE FORWARD RECTIFIED CURRENT,
AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE




PEAK FORWARD SURGE CURRENT,
AMPERES

FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT



INSTANTANEOUS FORWARD
CURRENT,AMPERES

FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



INSTANTANEOUS REVERSE CURRENT,
MILLIAMPERES

FIG. 4-TYPICAL REVERSE CHARACTERISTICS

