


1. Compatible with various 10/100 Base-TX transceiver requiring 1:1 transmit and receive turns ratio
2. Compliant with IEEE 802.3at standard including baseline wander compensation specification of 350 μ H OCL when Biased at 8mA
3. Designed to comply with the following requirements as defined by IEC60950-1: Reinforced insulation at a working volatage of 250Vrms.
4. Designed to comply with 10mm min.creepage and 7mm min. clearance as defined by IEC60601-1;2006
5. Operating Temperature range: -40 $^{\circ}$ C TO +85 $^{\circ}$ C
6. Storage temperature range: -40 $^{\circ}$ C TO +125 $^{\circ}$ C



DIMENSIONS & SCHEMATICS



All 16 terminals must lie on a plane within .004mm of surface a after lead tinning

TECHNICAL SPECIFICATIONS

Inductance :	350 μ H Min. @ 100 KHz, 100mV with 8mA DC Bias Lp(16-14)
	350 μ H Min. @ 100 KHz, 100mV with 8mA DC Bias Lp(11-9)
Turns Ratio($\pm 2\%$):	1CT:1CT,(1-3):(16-14)
	1CT:1CT,(6-8):(11-9)
Insertion Loss:	-1.5dB Max. @ 0.1M-100MHz
Return Loss:	-18dB Min. @ 0.5M-30MHz
	-15 dB Min. @ 30-45 MHz
	-13 dB Min.@ 45-60 MHz
	-10dB Min.@ 60-80 MHz
Cross Talk:	-40 dB Min.@ 1-100 MHz
Isolation HI-POT:	6000Vrms 1mA 60Second,7200Vrms 1mA 3Second

PACKING SPECIFICATION

