

安数光®

UK ISOCOM COMPONENTS LIMITED

## IS181x Series

### SOP4, DC Input Photo Transistor Coupler

#### Description

The IS181x series combine an AlGaAs infrared emitting diode as the emitter which is optically coupled to a silicon planar phototransistor detector in a plastic SOP4 package.

With the robust coplanar double mold structure, IS181x series provide the most stable isolation feature.


#### Features

- High isolation 3750 VRMS
  - CTR flexibility available see order information
  - DC input with transistor output
  - Operating temperature range - 55 °C to 110 °C
  - RoHS & REACH Compliance
  - Halogen free (Optional)
  - MSL class 1
    - UL - UL1577
    - VDE - EN60747-5-5(VDE0884-5)
    - CQC - GB4943.1, GB8898
    - cUL- CSA Component Acceptance
- Service Notice No. 5A

#### Applications

- Switch mode power supplies
- Programmable controllers
- Household appliances
- Office equipment


#### SCHEMATIC



#### PIN DEFINITION

1. Anode
2. Cathode
3. Emitter
4. Collector

#### PACKAGE OUTLINE



### ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	VALUE	UNIT	NOTE
INPUT				
Forward Current	$I_F$	60	mA	
Peak Forward Current	$I_{FP}$	1	A	1
Reverse Voltage	$V_R$	6	V	
Input Power Dissipation	$P_I$	100	mW	
OUTPUT				
Collector - Emitter Voltage	$V_{CEO}$	35	V	
Emitter - Collector Voltage	$V_{ECO}$	7	V	
Collector Current	$I_C$	50	mA	
Output Power Dissipation	$P_O$	150	mW	
COMMON				
Total Power Dissipation	$P_{tot}$	200	mW	
Isolation Voltage	$V_{iso}$	3750	Vrms	2
Operating Temperature	$T_{opr}$	-55~110	°C	
Storage Temperature	$T_{stg}$	-55~125	°C	
Soldering Temperature	$T_{sol}$	260	°C	

Note 1. 100μs pulse, 100Hz frequency


Note 2. AC For 1 Minute, R.H. = 40 ~ 60%

### ELECTRICAL OPTICAL CHARACTERISTICS at Ta=25°C

PARAMETER	SYMBOL	MIN	TYP.	MAX.	UNIT	TEST CONDITION	NOTE
INPUT							
Forward Voltage	$V_F$	-	1.24	1.4	V	$I_F=10\text{mA}$	
Reverse Current	$I_R$	-	-	10	$\mu\text{A}$	$V_R=6\text{V}$	
Input Capacitance	$C_{in}$	-	10	-	pF	$V=0, f=1\text{kHz}$	
OUTPUT							
Collector Dark Current	$I_{CEO}$	-	-	100	nA	$V_{CE}=20\text{V}, I_F=0$	
Collector-Emitter Breakdown Voltage	$BV_{CEO}$	35	-	-	V	$I_C=0.1\text{mA}, I_F=0$	
Emitter-Collector Breakdown Voltage	$BV_{ECO}$	7	-	-	V	$I_E=0.1\text{mA}, I_F=0$	
TRANSFER CHARACTERISTICS							
Current Transfer Ratio	IS181	CTR	50	-	600	$I_F=5\text{mA}, V_{CE}=5\text{V}$	
	IS181A		80	-	160		
	IS181B		130	-	260		
	IS181C		200	-	400		
	IS181GB		100	-	600		
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	-	0.06	0.2	V	$I_F=20\text{mA}, I_C=1\text{mA}$	
Isolation Resistance	$R_{ISO}$	$10^{12}$	$10^{14}$	-	$\Omega$	DC500V, 40 ~ 60% R.H.	
Floating Capacitance	$C_{IO}$	-	0.4	1	pF	$V=0, f=1\text{MHz}$	
Response Time (Rise)	$t_r$	-	3	18	$\mu\text{s}$	$V_{CE}=2\text{V}, I_C=2\text{mA}$	3
Response Time (Fall)	$t_f$	-	4	18	$\mu\text{s}$	$R_L=100\Omega$	3
Cut-off Frequency	$f_c$	-	80	-	kHz	$V_{CE}=2\text{V}, I_C=2\text{mA}$ $R_L=100\Omega, -3\text{dB}$	4

Note 3. Fig.12&13

Note 4. Fig.14



CHARACTERISTIC CURVES

Fig.1 Forward Current  
vs. Ambient Temperature




Fig.2 Collector Power Dissipation  
vs. Ambient Temperature




Fig.3 Forward Current  
vs. Forward Voltage




Fig.4 Collector Dark Current  
vs. Ambient Temperature




Fig.5 Collector Current  
vs. Collector-emitter Voltage







Fig.6 Collector Current  
vs. Collector-emitter Voltage






## CHARACTERISTIC CURVES


**Fig.7 Normalized Current Transfer Ratio vs. Forward Current**




**Fig.8 Normalized Current Transfer Ratio vs. Ambient Temperature**




**Fig.9 Collector-emitter Saturation Voltage vs. Ambient Temperature**



**Fig.10 Switching Time vs. Load Resistance**




**Fig.11 Frequency Response**




### TEST CIRCUITS


**Fig.12 Test Circuits of Response Time**




**Fig.13 Curves of Response Time**



**Fig.14 Test Circuits of Frequency Response**






安数光®

UK ISOCOM COMPONENTS LIMITED


**IS181x Series**


**SOP4, DC Input Photo Transistor Coupler**

**PACKAGE DIMENSIONS** (Dimensions in mm unless otherwise stated)



**Recommended Solder Mask** (Dimensions in mm unless otherwise stated)





安数光®


UK ISOCOM COMPONENTS LIMITED

**IS181x Series**


**SOP4, DC Input Photo Transistor Coupler**

**CARRIER TAPE SPECIFICATIONS (Dimensions in mm unless otherwise stated)**


**Option T1**



**Option T2**







安数光®



UK ISOCOM COMPONENTS LIMITED

**IS181x Series**

**SOP4, DC Input Photo Transistor Coupler**

**REEL SPECIFICATIONS** (Dimensions in mm unless otherwise stated)

**Option T1 & T2**



### ORDERING AND MARKING INFORMATION

#### MARKING INFORMATION



**I** : Company Abbr.  
**FPT2** : Part Number Code  
**Y** : Fiscal Year  
**WW** : Work Week  
**X** : CTR Rank

#### ORDERING INFORMATION


#### LABEL INFORMATION

### IS181x-Z

IS181 – Part Number  
 X – Rank (A/B/C/D or None)  
 Z – Tape and Reel Option  
 (None=T1 IS181xT2=T2)


#### PACKING QUANTITY

Option	Quantity	Quantity – Inner box	Quantity – Outer box
T1	3000 Units/Reel	3 Reels/Inner box	5 Inner box/Outer box = 45k Units
T2	3000 Units/Reel	3 Reels/Inner box	5 Inner box/Outer box = 45k Units




## REFLOW INFORMATION

### REFLOW PROFILE




Profile Feature	Sn-Pb Assembly Profile	Pb-Free Assembly Profile
Temperature Min. (T <sub>smin</sub> )	100	150°C
Temperature Max. (T <sub>smax</sub> )	150	200°C
Time (t <sub>s</sub> ) from (T <sub>smin</sub> to T <sub>smax</sub> )	60-120 seconds	60-120 seconds
Ramp-up Rate (t <sub>L</sub> to t <sub>P</sub> )	3°C/second max.	3°C/second max.
Liquidous Temperature (T <sub>L</sub> )	183°C	217°C
Time (t <sub>L</sub> ) Maintained Above (T <sub>L</sub> )	60 – 150 seconds	60 – 150 seconds
Peak Body Package Temperature	235°C +0°C / -5°C	260°C +0°C / -5°C
Time (t <sub>P</sub> ) within 5°C of 260°C	20 seconds	30 seconds
Ramp-down Rate (T <sub>P</sub> to T <sub>L</sub> )	6°C/second max	6°C/second max
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.



**TEMPERATURE PROFILE OF SOLDERING**

**WAVE SOLDERING (JESD22-A111 COMPLIANT)**



**HAND SOLDERING BY SOLDERING IRON**

Soldering Temperature	380+0/-5°C
Soldering Time	3 sec max.

- One time soldering is recommended for all soldering method.
- Do not solder more than three times for IR reflow soldering.

**DISCLAIMER**

- ASG is continually improving the quality, reliability, function and design. ASG reserves the right to make changes without further notices.
- The characteristic curves shown in this datasheet are representing typical performance which are not guaranteed.
- ASG makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, ASG disclaims (a) any and all liability arising out of the application or use of any product, (b) any and all liability, including without limitation special, consequential or incidental damages, and (c) any and all implied warranties, including warranties of fitness for particular
- The products shown in this publication are designed for the general use in electronic applications such as office automation, equipment, communications devices, audio/visual equipment, electrical application and instrumentation purpose, non-infringement and merchantability.
- This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or lifesaving applications or any other application which can result in human injury or death.
- Please contact ASG sales agent for special application request.
- Immerge unit's body in solder paste is not recommended.
- Parameters provided in datasheets may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated in each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify ASG's terms and conditions of purchase, including but not limited to the warranty expressed therein.
- Discoloration might be occurred on the package surface after soldering, reflow or long-time use. It neither impacts the performance nor reliability.