

SLIDE SWITCH

碩方精密電子開關


www.Sofng.com

Operation: SMT/立式 中大型 8PIN 三挡位 滑动开关 [柄长可定制]



ITEM NO.: MS-2346K-G□ (Series)

(L13.0mm×W3.5mm×H3.50mm SLIDE-SWITCH)



Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	0.3A, 30V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	300V AC for 1 minute	250 V AC for 1 minut
	There No Load	15,000 Cycles	10,000 Cycles
Durable Performance	Rated Load	12,000 Cycles	8,500 Cycles
	Storage temp.	-25℃~+75℃(Operating Temp:)	
	Operating Force	2. 6N. (1N. =100gram-force) ±0. 5N	
	Heat Rrsistance	IR Reflow:255℃, 5sec. Manual :350℃, 3sec.	

Material declaration		
No.	NAME	Description
1	拨柄	PA46 耐热尼龙塑料
2	盖板	C5191R-H 磷铜[镀银]
3	基座	LCP 30%G/F (Black)耐热塑胶
4	弹片	Beryllium bronze 铍青铜[单面镀银]
5	嵌件	C5191R-H 磷铜[镀银]

表面贴装 SMT


正向操作 DOWN

精密部品 NICETY

可靠 STABILIZE



適合環保 RoHS

CIRCUIT DIAGRAM



Unit:mm

P.C.B LAYOUT



MS-2346K - G*

产品型号

拨柄高度
G2=2.0mm
G3=3.0mm
G4=4.0mm

