





T:1.6 Dimensions of PC board holes
Tolerance : ±0.1(Printed-sided view)



REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

PROJECT		LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating		3A,24V DC	
	Initial Contact Resistance		50mΩ max.	
	Insulation Resistance		100MΩ min.500V DC Skey/PD : 100MΩ min.300V DC	
	Withstand Voltage		500V AC for 1 minute	350 V AC for 1 minut
Durable Performance	There No Load		6,000 Cycles	5,000 Cycles
	Rated Load		5,000 Cycles	4,000 Cycles
Storage temp.			-35℃~+75℃(Operating Temp:)	
Operating Force			IF:35N MAX. (EF:10.0N MIN.)	
Heat Rrsistance			IR Reflow:235℃,5sec. Manual :350℃,3sec.	

PIN	Part No.
内芯 1.0mm	DC-008-T10
内芯 1.1mm	DC-008-T11
内芯 1.3mm	DC-008-T13
内芯 1.65mm	DC-008-T16

Material declaration		
No	NAME	MATERIAL
①	主体	PBT/BLACK
②	后盖	PBT/BLACK
③	弹片	C5191R-H/t=0.25mm
④	弯钩	C5191R-H/t=0.30mm
⑤	平片	C5191R-H/t=0.30mm
⑥	内芯	H62

DIMENSION CLASSIFICATION
■ : CRITICAL
☒ : MAJOR

TOLERANCE TABLE

.X	±	0.40
.XX	±	0.25
.XXX	±	0.10
ANGLE	±	2°

台灣碩方精密電子科技有限公司
TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD

TITLE
DC-008 焊线式中小型电
源DC插座-带固定孔

PART NO.	DC-008	SERIES	SD106
APPROVED	Peck	DWG NO.	SOF-G006
CHECKED	Paul	SCALE	1:1
DRAWIN	David	UNIT	mm
REV	AO	SIZE	A4
SHEET NO.	1/1		

開關,連接器
SOFNG