

4

3

2

1

ROCKER SWITCH MODEL SS24(PCB TYPE;SINGLE POLE SINGLE THROW)

RATING: 12A 125/250VAC (C-UL)


16A 250VAC(C-UL)

16(4)A 250V~T125(VDE;NEMKO;SEMKO;DEMKO;FIMKO)


ALL MATERIAL USING MEET THE RoHS DIRECTIVE

"O" 表示关键尺寸 DENOTES CRITICAL DIMENSIONS



SCHEMATIC






PANEL CUTOUT DIMENSION



PANEL THICKNESS	X	Y
0.8~1.2mm	19.2 ^{+0.1} _{-0.1} mm	21.9 ^{+0.1} _{-0.1} mm
1.3~2.0mm	19.4 ^{+0.1} _{-0.1} mm	21.9 ^{+0.1} _{-0.1} mm
2.1~2.5mm	19.8 ^{+0.1} _{-0.1} mm	21.9 ^{+0.1} _{-0.1} mm



MOUNTING HOLE ARRANGEMENT



品名	柄的颜色	基座颜色
SS24-WBNNC-P20-R	原料白	黑色
SS24-WBNNC-P20-R(W1)	纯白色	黑色
SS24-BBNNC-P20-R	黑色	黑色



5		10		DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4		9		RANGE	TOLERANCE				LMC 2019.05.20	SCALE	NO		
3		8		X	±0.30					MAT'L	***		
2		7		X.X	±0.20					MATERIAL NO.		DRAWING NO.	REV.
1	增加品名 2024.03.14	6		X.XX	±0.10								
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.				SS24-BBNNC-P20-R	WIF120065	A1	

4

3

2

1