


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS: ANGLE $\pm 5^\circ$
UNIT: MM X. ± 0.38
X.X ± 0.25

BACKSHELL KIT INCLUDES:

- (2)BACKSHELL HALVES
- (3)4-40 THUMBSCREWS
- (2)CLAMP SCREWS
- (2)CLAMP
- (1)BLANKING PLUG
- (1)SET OF COMPRESSION INSERTS-VARIOUS SIZES FOR 9-37



DIMENSIONS(mm/in)

SIZE	A $\begin{smallmatrix} +1.6(+.063) \\ -.50(-.02) \end{smallmatrix}$	B $\begin{smallmatrix} +1.1(+.043) \\ -.50(-.02) \end{smallmatrix}$	C $\begin{smallmatrix} +.80(+.032) \\ -.50(-.02) \end{smallmatrix}$	D $\begin{smallmatrix} \pm.50 \\ \pm.02 \end{smallmatrix}$
9	31.5	40.0	15.00	24.99
	1.240	1.575	0.591	0.984
15	40.0	40.0	15.00	33.32
	1.575	1.575	0.591	1.312
25	53.5	43.0	15.00	47.04
	2.106	1.693	0.591	1.852

ORDERING INFORMATON:

SIZE	P/N - KITTED	PRODUCT CODE
9-WAY	6260-0106-01	MHDSSK-M-9-L-K
15-WAY	6260-0106-02	MHDSSK-M-15-L-K
25-WAY	6260-0106-03	MHDSSK-M-25-L-K

BACKSHELL MATERIAL: ABS,UL RECOGNIZED
PLATING: NICKEL
JACKSCREWS: STEEL:ZN PLATED WITH PLASTIC KNOB
MATING SCREW: STEEL:ZN PLATED
BLANKING PLUG: ABS,UL RECOGNIZED
COMPRESSION INSERT: ABS,UL RECOGNIZED
METAL CLAMP: STEEL:ZN PLATED
PLASTIC CLAMP: ABS,UL RECOGNIZED,NICKEL PLATED
CLAMP SCREW: STEEL:ZN PLATED
OPERATING TEMP: -55°C TO+110°C

THESE DRAWINGS AND SPECIFICATIONS ARE THE
PROPERTY OF MH CONNECTORS AND SHALL NOT BE
REPRODUCED, COPIED OR USED AS THE BASIS FOR
THE MANUFACTURE OR SALE OF APPARATUS WITHOUT
WRITTEN PERMISSION.

DRAWN
Johnny
DATE
11-24-15

APPROVED
Victor Lin
DATE
11-24-15

SCALE
1 : 1
SHEET OF
1 OF 1
REV:
3.0

DRAWING No
MHDSSK-M-XX-L



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.



**MH CONNECTORS ,
DIVISION OF EDAC**