



<b>V<sub>(BR)DSS</sub></b>	<b>R<sub>DS(on)Max</sub></b>	<b>I<sub>D Max</sub></b>
60V	17mΩ@10V	50A

**TO-252**


## Features

- R<sub>DS(ON)</sub> ≤ 17m Ω @ V<sub>GS</sub>=10V, I<sub>D</sub>=20A
- High Switching Speed
- Improved dv/dt capability

## Marking




XXX: Date Code

## Application

- Switching application

## Equivalent Circuit



## Absolute Maximum Ratings (T<sub>A</sub>=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V <sub>DS</sub>	60	V
Gate-Source Voltage	V <sub>GS</sub>	±20	V
Continuous Drain Current	I <sub>D</sub>	50	A
Pulsed Drain Current (Note 2)	I <sub>DM</sub>	200	A
Avalanche Energy Single Pulsed (Note 3)	E <sub>AS</sub>	98	mJ
Peak Diode Recovery dv/dt	dv/dt	10	A
Power Dissipation	P <sub>D</sub>	62.5	W
Thermal Resistance from Junction to Ambient	R <sub>θJA</sub>	62	°C/W
Thermal Resistance from Junction to Case	R <sub>θJC</sub>	2	°C/W
Junction Temperature	T <sub>J</sub>	150	°C
Storage Temperature	T <sub>stg</sub>	-50 ~+150	°C

Notes:

1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.
2. Repetitive Rating : Pulse width limited by maximum junction temperature.
- 3.L=43mH, IAS=43A, VDD=25V, RG=20Ω, Starting TJ=25°C
- 4.ISD ≤ 30A, VDS=0V, di/dt ≤ 200A/μs, VDD ≤ BVDSS, Starting TJ = 25°C

**T<sub>a</sub> = 25°C unless otherwise specified**

Symbol	Parameter	Condition	Min	Typ	Max	Unit
<b>V<sub>(BR)DSS</sub></b>	Drain-Source Breakdown Voltage	<b>V<sub>GS</sub>=0V, I<sub>D</sub>=250μA</b>	60	--	--	V
<b>I<sub>GS</sub></b>	Gate-Source Leakage Current	<b>V<sub>GS</sub>=±20V, V<sub>DS</sub>=0V</b>	--	--	±100	nA
<b>I<sub>DSS</sub></b>	Drain-Source Leakage Current	<b>V<sub>DS</sub>=60V, V<sub>GS</sub>=0V</b>	--	--	1	uA
<b>V<sub>GS(TH)</sub></b>	Gate Threshold Voltage	<b>V<sub>DS</sub>=V<sub>GS</sub>, I<sub>D</sub>=250μA</b>	1.2	1.8	2.5	V
<b>R<sub>Ds(on)</sub></b>	Drain-Source On-State Resistance	<b>V<sub>GS</sub>=10V, I<sub>D</sub>=20A</b>	--	12	17	mΩ
		<b>V<sub>GS</sub>=4.5V, I<sub>D</sub>=20A</b>	--	17	23	mΩ

## Dynamic Electrical Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
<b>C<sub>iss</sub></b>	Input Capacitance	<b>V<sub>DS</sub>=30V</b> <b>V<sub>GS</sub>=0V</b> <b>f=1MHz</b>	--	1889	--	pF
<b>C<sub>oss</sub></b>	Output Capacitance		--	113	--	pF
<b>C<sub>rss</sub></b>	Reverse Transfer Capacitance		--	92	--	pF
<b>Q<sub>g</sub></b>	Total Gate Charge	<b>V<sub>DS</sub>=30V,</b> <b>V<sub>GS</sub>=10V,</b> <b>I<sub>D</sub>=20A (Note1,2)</b>	--	40	--	nC
<b>Q<sub>gs</sub></b>	Gate Source Charge		--	7.8	--	nC
<b>Q<sub>gd</sub></b>	Gate Drain Charge		--	8.3	--	nC

## Switching Characteristics


Symbol	Parameter	Condition	Min	Typ	Max	Unit
<b>t<sub>d(on)</sub></b>	Turn on Delay Time	<b>V<sub>DS</sub>=30V,</b> <b>V<sub>GS</sub>=10V,</b> <b>I<sub>D</sub>=20A,</b> <b>R<sub>G</sub>=3Ω (Note1,2)</b>	--	13	--	ns
<b>t<sub>r</sub></b>	Turn on Rise Time		--	25	--	ns
<b>t<sub>d(off)</sub></b>	Turn Off Delay Time		--	60	--	ns
<b>t<sub>f</sub></b>	Turn Off Fall Time		--	9	--	ns

## Source Drain Diode Characteristics


Symbol	Parameter	Condition	Min	Typ	Max	Unit
<b>I<sub>SD</sub></b>	Source drain current(Body Diode)		--	--	50	A
<b>V<sub>SD</sub></b>	Drain-Source Diode Forward Voltage	<b>I<sub>S</sub>=20A, V<sub>GS</sub>=0V</b>	--	--	1.2	V
<b>t<sub>rr</sub></b>	Body Diode Reverse Recovery Time	<b>I<sub>S</sub>=20A,</b> <b>V<sub>GS</sub>=0V,</b> <b>dI<sub>S</sub>/dt=100A/μs</b>	--	29	--	ns
<b>Q<sub>rr</sub></b>	Body Diode Reverse Recovery Charge		--	21	--	nC

- Notes:**
1. Pulse test ; Pulse width 300us, duty cycle 2%.
  2. Essentially independent of operating temperature.


**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted




**Figure 1. Maximum Safe Operating Area**




**Figure 2. Maximum Power Dissipation vs Case Temperature**









**Figure 3. Maximum Continuous Drain Current vs Case Temperature**




**Figure 4. Typical output Characteristics**




**Figure 5. Maximum Effective Thermal Impedance, Junction to Case**

**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted

**Figure 6. Typical Transfer Characteristics**

**Figure 7. Typical Body Diode Transfer Characteristics**

**Figure 8. Drain-to-Source On Resistance vs Drain Current**

**Figure 9. Normalized On Resistance vs Junction Temperature**

**Figure 10. Normalized Threshold Voltage vs Junction Temperature**

**Figure 11. Normalized Breakdown Voltage vs Junction Temperature**




**Typical Characteristics**  $T_J = 25^\circ\text{C}$ , unless otherwise noted




**Figure 12. Capacitance Characteristics**



**Figure 13. Typical Gate Charge vs  
Gate to Source Voltage**

**Figure A: Gate Charge Test Circuit and Waveform**

**Figure B: Resistive Switching Test Circuit and Waveform**

**Figure C: Unclamped Inductive Switching Test Circuit and Waveform**



## Outline Drawing

TO-252 Package Outline Dimensions


TO-252(D-PAK) mechanical data

UNIT	A	B	b	C	D	E	F	G	H	L	L1	L2	L3	S	M	N	J	K	T	
mm	max	6.7	5.5	0.8	2.5	6.3	0.6	1.8	2.29	0.55	3.1	1.2	1.0	1.75	0.1	1.8	1.3	3.16	1.80	4.83
	min	6.3	5.1	0.3	2.1	5.9	0.4	1.3		0.45	2.7	0.8	0.6	1.40	0.0					
mil	max	264	217	31	98	248	24	71	90	22	122	47	39	69	4	71	51	124	71	190
	min	248	201	12	83	232	16	51		18	106	31	24	55	0					

## Suggested Pad Layout



## Note:

1. Controlling dimension: in millimeters.
2. General tolerance:  $\pm 0.05$  mm.
3. The pad layout is for reference purposes only.