






E	1		2		3		4		5		6		7		8																																																																																																																																																																			
	SAMZO		REAC/ROHS								REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE																																																																																																																																																																		
											A1	NEW	Replace frame			2013.06.21																																																																																																																																																																		
D	SPECIFICATIONS														RECOMMEND P.C.B LAYOUT PCB TOLERANCE: ±0.05 (TOP VIEW)		<table><tr><td>Options</td><td>PA</td><td>PC</td><td>H</td><td>L</td></tr><tr><td>Standard</td><td>4.0</td><td>2.2</td><td>2.0</td><td>8.2</td></tr><tr><td>Specified</td><td></td><td></td><td></td><td></td></tr></table>		Options	PA	PC	H	L	Standard	4.0	2.2	2.0	8.2	Specified																																																																																																																																																					
	Options	PA	PC	H	L																																																																																																																																																																													
	Standard	4.0	2.2	2.0	8.2																																																																																																																																																																													
	Specified																																																																																																																																																																																	
Current Rating: 1.0 Amps Withstanding Voltage: AC 500V Insulation Resistance:1000M Ω Min Contact Resistance: 20 mΩ Max Operation Temperature:-40 ° to+105 ° Insrlator Material: Polyester(UL94V-0) Contact Material: Brass Standard: PA6T Contact Plating: Gold Flash Max.Processing Temp: 240 ° C for30-60seconds (260 ° C for5seconds)																																																																																																																																																																																		
C	Code Description														<table><tr><td>No. of Contacts</td><td colspan="2">DIME NSIONS</td><td>No. of Contacts</td><td colspan="2">DIME NSIONS</td></tr><tr><td></td><td>A</td><td>B</td><td></td><td>A</td><td>B</td></tr><tr><td>1</td><td>0</td><td>1.27</td><td>26</td><td>31.75</td><td>33.02</td></tr><tr><td>2</td><td>1.27</td><td>2.54</td><td>27</td><td>33.02</td><td>34.29</td></tr><tr><td>3</td><td>2.54</td><td>3.81</td><td>28</td><td>34.29</td><td>35.56</td></tr><tr><td>4</td><td>3.81</td><td>5.08</td><td>29</td><td>35.56</td><td>36.83</td></tr><tr><td>5</td><td>5.08</td><td>6.35</td><td>30</td><td>36.83</td><td>38.10</td></tr><tr><td>6</td><td>6.35</td><td>7.62</td><td>31</td><td>38.10</td><td>39.37</td></tr><tr><td>7</td><td>7.62</td><td>8.89</td><td>32</td><td>39.37</td><td>40.64</td></tr><tr><td>8</td><td>8.89</td><td>10.16</td><td>33</td><td>40.64</td><td>41.91</td></tr><tr><td>9</td><td>10.16</td><td>11.43</td><td>34</td><td>41.91</td><td>43.18</td></tr><tr><td>10</td><td>11.43</td><td>12.70</td><td>35</td><td>43.18</td><td>44.45</td></tr><tr><td>11</td><td>12.70</td><td>13.97</td><td>36</td><td>44.45</td><td>45.72</td></tr><tr><td>12</td><td>13.97</td><td>15.24</td><td>37</td><td>45.72</td><td>46.99</td></tr><tr><td>13</td><td>15.24</td><td>16.51</td><td>38</td><td>46.99</td><td>48.26</td></tr><tr><td>14</td><td>16.51</td><td>17.78</td><td>39</td><td>48.26</td><td>49.53</td></tr><tr><td>15</td><td>17.78</td><td>19.05</td><td>40</td><td>49.53</td><td>50.80</td></tr><tr><td>16</td><td>19.05</td><td>20.32</td><td>41</td><td>50.80</td><td>52.07</td></tr><tr><td>17</td><td>20.32</td><td>21.59</td><td>42</td><td>52.07</td><td>53.34</td></tr><tr><td>18</td><td>21.59</td><td>22.86</td><td>43</td><td>53.34</td><td>54.61</td></tr><tr><td>19</td><td>22.86</td><td>24.13</td><td>44</td><td>54.61</td><td>55.88</td></tr><tr><td>20</td><td>24.13</td><td>25.40</td><td>45</td><td>55.88</td><td>57.15</td></tr><tr><td>21</td><td>25.40</td><td>26.67</td><td>46</td><td>57.15</td><td>58.42</td></tr><tr><td>22</td><td>26.67</td><td>27.94</td><td>47</td><td>58.42</td><td>59.69</td></tr><tr><td>23</td><td>27.94</td><td>29.21</td><td>48</td><td>59.69</td><td>60.96</td></tr><tr><td>24</td><td>29.21</td><td>30.48</td><td>49</td><td>60.96</td><td>62.23</td></tr><tr><td>25</td><td>30.48</td><td>31.75</td><td>50</td><td>62.23</td><td>63.50</td></tr></table>		No. of Contacts	DIME NSIONS		No. of Contacts	DIME NSIONS			A	B		A	B	1	0	1.27	26	31.75	33.02	2	1.27	2.54	27	33.02	34.29	3	2.54	3.81	28	34.29	35.56	4	3.81	5.08	29	35.56	36.83	5	5.08	6.35	30	36.83	38.10	6	6.35	7.62	31	38.10	39.37	7	7.62	8.89	32	39.37	40.64	8	8.89	10.16	33	40.64	41.91	9	10.16	11.43	34	41.91	43.18	10	11.43	12.70	35	43.18	44.45	11	12.70	13.97	36	44.45	45.72	12	13.97	15.24	37	45.72	46.99	13	15.24	16.51	38	46.99	48.26	14	16.51	17.78	39	48.26	49.53	15	17.78	19.05	40	49.53	50.80	16	19.05	20.32	41	50.80	52.07	17	20.32	21.59	42	52.07	53.34	18	21.59	22.86	43	53.34	54.61	19	22.86	24.13	44	54.61	55.88	20	24.13	25.40	45	55.88	57.15	21	25.40	26.67	46	57.15	58.42	22	26.67	27.94	47	58.42	59.69	23	27.94	29.21	48	59.69	60.96	24	29.21	30.48	49	60.96	62.23	25	30.48	31.75	50	62.23	63.50
	No. of Contacts	DIME NSIONS		No. of Contacts	DIME NSIONS																																																																																																																																																																													
		A	B		A	B																																																																																																																																																																												
	1	0	1.27	26	31.75	33.02																																																																																																																																																																												
2	1.27	2.54	27	33.02	34.29																																																																																																																																																																													
3	2.54	3.81	28	34.29	35.56																																																																																																																																																																													
4	3.81	5.08	29	35.56	36.83																																																																																																																																																																													
5	5.08	6.35	30	36.83	38.10																																																																																																																																																																													
6	6.35	7.62	31	38.10	39.37																																																																																																																																																																													
7	7.62	8.89	32	39.37	40.64																																																																																																																																																																													
8	8.89	10.16	33	40.64	41.91																																																																																																																																																																													
9	10.16	11.43	34	41.91	43.18																																																																																																																																																																													
10	11.43	12.70	35	43.18	44.45																																																																																																																																																																													
11	12.70	13.97	36	44.45	45.72																																																																																																																																																																													
12	13.97	15.24	37	45.72	46.99																																																																																																																																																																													
13	15.24	16.51	38	46.99	48.26																																																																																																																																																																													
14	16.51	17.78	39	48.26	49.53																																																																																																																																																																													
15	17.78	19.05	40	49.53	50.80																																																																																																																																																																													
16	19.05	20.32	41	50.80	52.07																																																																																																																																																																													
17	20.32	21.59	42	52.07	53.34																																																																																																																																																																													
18	21.59	22.86	43	53.34	54.61																																																																																																																																																																													
19	22.86	24.13	44	54.61	55.88																																																																																																																																																																													
20	24.13	25.40	45	55.88	57.15																																																																																																																																																																													
21	25.40	26.67	46	57.15	58.42																																																																																																																																																																													
22	26.67	27.94	47	58.42	59.69																																																																																																																																																																													
23	27.94	29.21	48	59.69	60.96																																																																																																																																																																													
24	29.21	30.48	49	60.96	62.23																																																																																																																																																																													
25	30.48	31.75	50	62.23	63.50																																																																																																																																																																													
B	A. 名称: 5A-排针 B. 间距: I-1.27mm C. 方式: L-180° DIP D. 塑高(H): 3-2.0mm E:总长(L): 82-8.2mm F:针长(PA): 40-4.0 G:针数: 202-2*2P(2-50PIN) H:定位: W-无定位 I:物料编码: 0-常规												The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		TITLE:: 1.27PH 2*NP H2.0 PC2.2 180°DIP																																																																																																																																																																			
	DWG NO: 5AIL3-P824001																																																																																																																																																																																	
	5A I L 3 - 82 40 - 2** - W 0 A B C D E F G H I										SCALE 1:1 UNIT mm		PART NO: 5AIL3180910																																																																																																																																																																					
	A	ITEM		DESCRIPTION		MATERIAL		QTY		FINSH/COLOR		GENERAL TOLERANCE		SAMZO COMPONENTS Electronic switch and connector manufacturer		MODEL NO: 5AIL3-8240-2NP-W0 NAME: PIN-H CONNECTOR																																																																																																																																																																		
1		针		黄铜		N		镀金																																																																																																																																																																										
2		主体		PA6T		1		黑色		≥0~2< ±0.15																																																																																																																																																																								
										DESIGN WANGGUIFA 2018.06.12 ≥2~5< ±0.25																																																																																																																																																																								
										CHECKED ZHENGUILAN 2018.06.12 ≥0~2< ±0.15																																																																																																																																																																								
										APPROVED LILIANJIANG 2018.06.14 ≥5 ±0.35																																																																																																																																																																								
1		2		3		4		5		6		7		8																																																																																																																																																																				