

4

3

2

1

ROCKER SWITCH MODEL SS24(PCB TYPE;SINGLE POLE SINGLE THROW)

RATING: 12A 125/250VAC (C-UL)




16A 250VAC(C-UL)

16(4)A 250V~T125(VDE;NEMKO;SEMKO;DEMKO;FIMKO)


ALL MATERIAL USING MEET THE RoHS DIRECTIVE

"○"表示关键尺寸 DENOTES CRITICAL DIMENSIONS




邮箱: hooya89@hooya.hk

MOUNTING HOLE
ARRANGEMENT

PANEL CUTOUT DIMENSION



PANEL THICKNESS	X	Y
0.8~1.2mm	19.2 ⁺⁰ _{-0.1} mm	21.9 ^{+0.1} ₋₀ mm
1.3~2.0mm	19.4 ⁺⁰ _{-0.1} mm	21.9 ^{+0.1} ₋₀ mm
2.1~2.5mm	19.8 ⁺⁰ _{-0.1} mm	21.9 ^{+0.1} ₋₀ mm



品名	柄的颜色	基座颜色
SS24-WBNNC-P20-R	原料白	黑色
SS24-WBNNC-P20-R(W1)	纯白	黑色

5	10	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
4	9	RANGE	TOLERANCE				LMC	SCALE	NO			
3	8	X	±0.30				2019.05.20	MAT'L	***			
2	7	X.X	±0.20					MATERIAL NO.				
1	6	X.XX	±0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.			SS24-WBNNC-P20-R(W1)	WIF120065	A0	

4

3

2

1