






- 1.CIRCUIT: ON/OFF
2." $\bigcirc$ "DENOTES CRITICAL DIMENSIONS.
3.Operation force: 800 $\pm$ 300gf
4.RATING:16A GP 125/250VAC 3/4HP 125/250VAC T125(CUL)
16(4)A 125/250V~ T125/55(ENEC17;NEMKO;CB)
6(4)A 250~ T125/55(CQC)
5.Contact resistance: <50m Ω
6.Insulation resistance: >100M Ω (500VDC between open contacts)
7.Dielectric strength: >1500Vac 0.5mA 1 minute
8.ACTUATOR COLOR:WHITE
HOUSING COLOR:WHITE
BASE COLOR:BLACK
9.ALL MATERIALS ARE ROHS COMPLIANT



PANEL CUTOUT DIMENSION:



Detent position



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		DRAWING NO.	REV.
4	→	9	→	RANGE	TOLERANCE				LMC	SCALE	NO			
3	→	8	→	X	±0.30				2023.10.14	MAT'L	***			
2	→	7	→	X.X	±0.20					MATERIAL NO.				
1	→	6	→	X.XX	±0.10									
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	LEGION ELECTRONIC & HARDWARE CO., LTD.				MPS21-WWBCA-A		WIF123076 A0		