


Surface Mount Schottky Rectifier




Features

- Low profile package
- Ideal for automated placement
- Guardring for overvoltage protection
- Low power losses, high efficiency
- High forward surge capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Part no. with suffix "Q" means AEC-Q101 qualified

Typical Applications

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, automotive and polarity protection applications.



Mechanical Data

- **Package:** DO-214AC (SMA)
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant, halogen-free
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Cathode line denotes the cathode end

■Maximum Ratings (T_a=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SS18AQ	SS110AQ
Device marking code			SS18A	SS110A
Repetitive peak reverse voltage	V _{RRM}	V	80	100
Maximum RMS voltage	V _{RMS}	V	56	70
Maximum DC blocking voltage	V _{DC}	V	80	100
Maximum average forward rectified current at T _L (Fig.1)	I _O	A	1.0	
Surge(non-repetitive)forward current @60Hz half-sine wave, 1 cycle, T _J =25°C	I _{FSM}	A	40	
Voltage rate of change (rated V _R)	dV/dt	V/μs	10000	
Storage temperature	T _{stg}	°C	-55~+175	
Junction temperature	T _J	°C	-55~+175	

■Electrical Characteristics(T_a=25°C Unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS		TYP	MAX	UNIT
Instantaneous forward voltage	V _F	I _F =1A	T _J =25°C	0.73	0.77	V
			T _J =125°C	-	0.68	
Reverse current	I _R	Rated V _R	T _J =25°C	-	1	μA
			T _J =125°C	-	0.5	mA
Typical junction capacitance	C _J	V _R =4V, f=1MHz		50	-	pF



■ Thermal Characteristics ($T_a=25^{\circ}\text{C}$ Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SS18AQ	SS110AQ
Thermal resistance	$R_{\theta J-A}$	$^{\circ}\text{C}/\text{W}$	65 ⁽¹⁾	
	$R_{\theta J-L}$		20 ⁽¹⁾	

Note

(1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pad areas

■ Characteristics (Typical)

Fig.1:Forward Current Derating Curve




Fig.2:Maximum Non-Repetitive Peak Forward Surge Current




Fig.3:Typical Instantaneous Forward Characteristics





Fig.4:Typical Reverse Leakage Characteristics




■ Ordering Information (Example)

PREFERRED P/N	PACKAGE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
SS18AQ-SS110AQ	SMA	Approximate 0.067	7500	120000	13" reel




■ Outline Dimensions



DO-214AC(SMA)		
Dim	Min	Max
A	1.25	1.58
B	2.40	2.83
C	4.06	4.75
D	1.90	2.30
E	4.93	5.28
F	0.76	1.41
G	0.08	0.20
H	0.15	0.31

■Suggested Pad Layout



DO-214AC(SMA)	
Dim	Millimeters
P1	4.00
P2	1.50
P3	6.50
Q1	2.50
Q2	1.70

