





P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC 12V 1A.
- 2.Contact resistance: $\leq 50\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
- 4.Withstanding voltage: 500VAC .
- 5.Insertion and extraction force: 5-30N.
- 6.Life test: 5,000 cycles.
- 7.Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.

				TOLERANCE UNLESS SPECIFIED							
7	HOUSING	PA9T	1								
6	SLEEVE	BRASS	1	Au-PLATED	<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$					
5	CONTACT 12#	PHOSPHOR BRONZE	1	Au-PLATED			NO	DATE	REVISIONS	BY	APPD
4	CONTACT 11#	BRASS	1	Au-PLATED	TITLE: PHONE JACK			UNIT : MM	ROHS	DWN	
3	CONTACT 10#	QBN2	1	Au-PLATED	MODEL: PJ-4506B-01-Z			SCALE: 1:1	COMPLIANT	CHK'D	
2	CONTACT 9#	QBN2	1	Au-PLATED						APPD	
1	CONTACT 1#~8#	QBN2	8	Au-PLATED							
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL:	⏏	REV :A0



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司