


RoHS  
Compatible

| REV. | DESCRIPTION | DATE       |
|------|-------------|------------|
| △    | 首次发行        | 2024-03-29 |
|      |             |            |



| 编号 | 图号       | 名称        | 材料 | 件数 | 备注 |
|----|----------|-----------|----|----|----|
| 1  | 外壳       | 黄铜Hpb59-1 | 镀镍 | 1  |    |
| 2  | 内导体(PIN) | 黄铜Hpb59-1 | 镀金 | 1  |    |
| 3  | 绝缘子      | 聚四氟乙烯     | -  | 1  |    |
| 4  |          |           |    |    |    |
| 5  |          |           |    |    |    |
| 6  |          |           |    |    |    |
| 7  |          |           |    |    |    |

Remark:

- Impedance standard 50  $\Omega$
- Band range DC0~6G
- Voltage VSWR 1.3MAX
- Voltage rating 500 VRMS(Maximum sea level)
- Dielectric withstand voltage 1500 VRMS (Sea level minimum)
- Insulation resistance 500 MEGOHMS
- Operating temperature -55 $^{\circ}$ C~+155 $^{\circ}$ C
- Relative temperature  $\leq 95\%$  (temperature 40 $^{\circ}$ C+2 $^{\circ}$ C)
- The surface products are ROHS compliant



东莞市众驰电子科技有限公司

Dongguan Zhongchi Electronic Technology Co.,Ltd Tel:0769-81238620 Fax:0769-81238620

PART NAME: MMCX-KHD


PART NO.: ZC6.61KE

DATE: 2024-03-29

APPROVED BY

CHECKED BY

DESIGNED BY



Tolerance

UNITS: mm

X.X  $\pm 0.1$

SCALE: 1/1

X.XX  $\pm 0.05$

REVISION: A

X $^{\circ}$   $\pm 1^{\circ}$