


Common Mode Power line Choke FC-DLFW2015-5mH-20A-LF

Features:


1. High current common mode choke
2. Broadband suppression for common mode noise
3. Custom designs on request
4. Inductance range: 5.0mH
5. Insulation Test Voltage: 1500VAC
6. turns Ratio: 1:1
7. Rated Current: 20A
8. Operating temperature: -40°C to $+125^{\circ}\text{C}$




1. Dimensions:mm



2. Schematic:



3. Recommended Land Pattern: mm



4. Electrical Properties

NO.	ITEMS	MEASURING POINT	TECHNICAL DATA	TEST CONDITION	INSTRUMENT
1	Inductance	N1=N2	2.0mH~5.0mH~8.0mH/typ	1KHz, 0.3V, 25°C	HP4284A
2	IR	COIL~CORE	100Mohm MIN	DC500V	MF2511
3	turns Ratio	N1:N2	1:1	20KHz, 1V, 25°C	TH3250
4	DCR	N1=N2	4.0mΩ TYP~6.5mΩ MAX	25°C	CH502
5	Insulation Test Voltage	COIL~COIL	1500V/AC	50Hz 3mA 5S	CJ2670
		COIL~CORE	500V/AC	50Hz 3mA 5S	CJ2670
6	Rated Current	N1/N2	20A	$\Delta T \leq 40^{\circ}\text{C}$ ($T_a=25^{\circ}\text{C}$)	WK3225B

Ambient temperature : -40°C to $+85^{\circ}\text{C}$

Operating temperature: -40°C to $+125^{\circ}\text{C}$