







NOTE:

1.MATERIAL:

1.1 INSULATOR:LCP UL94V-0

1.2 CONTACT:BRONZE

1.3 SHELL:BRASS

2.ELECTRICAL CHARACTERISTICS:

2.1 CONTACT RESISTANCE:30m2 MAXIMUM

2.2CONTACT CURRENT RATING:1.5A

2.3DIELECTRIC WITHSTANDING VOLTAGE

100 VAC RM.S.

2.4 INSULATION RESISTANCE 100 MEGOHMS MIN

2.5 OPERATING TEMPERATURE:-40ïC ix 85ïC

3.MECHANICAL CHARACTERISTICS:

3.1 MATING FORCE:3.57kgf MAX

3.2UNMATED FORCE:0.82kgf MIN AFTER TEST

3.3 DURABILITY MANDATORY:1200 CYCLES

4.PLATING


4.1 TERMINAL:

50u"MIN NICKEL ALL OVER

80U"MIN Tin ON SOLDER AREA

(1i<30)U"Au ON CONTACT AREA

4.2 SHELL:100U"MIN.NICEL ALL OVER



REFERENCE PCB LAYOUT

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: USB3.0 AF 卷边
			PAR USB-313-ACSY
DECIMALS:	ANGLES:		DWN
.X:±0.30	.X":±3°		CHKD
.XX:±0.20	.XX":±2°		APVD
.XXX:±0.10			SCALE1:1 UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A