







N ON END			95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	2-111446-6	
			89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	2-111446-5	
			70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	2-111446-4	
			65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	2-111446-3	
			57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	2-111446-2	
			52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	2-111446-1	
			47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	2-111446-0	
			45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	1-111446-9	
			39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	1-111446-8	
			78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-7	
			34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16	1-111446-6	
			32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	1-111446-5	
AREA		27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	1-111446-4		
		SUPERCEDED		95.81 [3.772]	86.21 [3.394]	39.37 [1.550]	31	63	64	1-111446-3
		OBSOLETE		89.59 [3.527]	81.13 [3.194]	36.83 [1.450]	29	59	60	1-111446-2
		OBSOLETE		78.03 [3.072]	68.43 [2.694]	30.48 [1.200]	24	49	50	1-111446-1
		OBSOLETE		70.41 [2.772]	60.81 [2.394]	26.67 [1.050]	21	43	44	1-111446-0
		OBSOLETE		65.33 [2.572]	55.73 [2.194]	24.13 [.950]	19	39	40	111446-9
		OBSOLETE		57.71 [2.272]	48.11 [1.894]	20.32 [.800]	16	33	34	111446-8
		SUPERCEDED		52.63 [2.072]	43.03 [1.694]	17.78 [.700]	14	29	30	111446-7
		OBSOLETE		47.55 [1.872]	37.95 [1.494]	15.24 [.600]	12	25	26	111446-6
		OBSOLETE		45.01 [1.772]	35.41 [1.394]	13.97 [.550]	11	23	24	111446-5
	B 5]			39.93 [1.572]	30.33 [1.194]	11.43 [.450]	9	19	20	111446-4
			OBSOLETE		34.85 [1.372]	25.25 [.994]	8.89 [.350]	7	15	16
		OBSOLETE		32.31 [1.272]	22.71 [.894]	7.62 [.300]	6	13	14	111446-2
			27.230 [1.072]	17.63 [.694]	5.08 [.200]	4	9	10	111446-1	
		CONTACT FINISH	E	D	C	B	A	NO. OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: H. MOLL 7-11-90 CHG: F.M. HEINRY 8-1-90 APVD: D. HOFFMAN 8-3-90		 TE Connectivity	
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 2 PLC ± 0.1% (.005) 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH: CONTACTS: SEE TABLE		NAME: UNIV I/O PIN CONN. WITHOUT MOUNTING EARS, AMP-LATCH™ SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:	
MATERIAL: 		PRODUCT SPEC: 108-1336 APPLICATION SPEC: 114-7011 WEIGHT: -		A1 00779 C-11144	
CUSTOMER DRAWING		SCALE: 4:1		SHEET 1 OF 1 REV R	