





P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50gf$
- 6.life test: 50,000 cycles.
- 7.Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
- 8Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	1						
							NO	DATE	REVISIONS			BY	APPD
4	CONTACT FOOT	BRASS	2	Ag-Plated	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	COAT	BRASS	1	Ag-Plated	MODEL: TS-1112E-C 1.8				SCALE: 1:1	COMPLIANT	CHK'D		
2	BUTTON	LCP	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOOYA 东莞市弘皓电子有限公司						APPD		
1	HOUSING	PA9T	1										
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:  				REV :A0