



1. FIGURE AND DIMENSIONS (视图及尺寸)



Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	5000
2. Working Temperature (温度)	-55~+150°
3. IP Rating (防护级别)	IP 50
4. Diameter of socket end(插入端直径)	ø 1.3
5. Rated voltage (额定电压)	1650V
6. Rated Current (额定电流)	11A
7. Shell material (壳体材质)	PC
8. Pin Material (插针材料)	Copper alloy gold plating(铜合金镀金)
9. Insulation resistance (绝缘电阻)	>100MΩ
10. Insulator material (绝缘体材料)	L: PPS, P: PEEK
11. Salt spray test (盐雾测试)	> 72H

Sum up (总结)	
Series (系列)	MI9
Shell style/model (外壳样式/型号)	LPAG: Straight plug, cable collet and nut for fitting a bend relief直塞、电缆夹头和螺母，用于安装弯曲凸起
Button (按键)	3 button(3个按键)
Termination type (终止类型)	Male solder (公焊锡)
Line diameter awg(线材直径)	28AWG-20AWG
Matching parts(配件)	-
14. Nut color (螺帽颜色)	G=灰色/J=黄色/A=蓝色/N=黑色/R=红色/V=绿色/B=白色

版本		TITLE		DRAWING NO.		REV.	
REVA4				LPAB. M1. 7. GLAG92H		A0	
REVA3							
REVA2							
REVA1							
DRAW							
CHECK		DATE		USE		XKB INDUSTRIAL PRECISION CO., LIMITED	
APPR'D		DATE					
		DATE					
PART NO.				UNIT	mm		
				SCALE	Free		
				SHEET	1 OF N		