



**SPECIFICATIONS**  
 Current Rating:0.75 Amps  
 Withstanding Voltage:AC 500V  
 Insulation Resistance:1000MΩ Min  
 Contact Resistance:20mΩ Max  
 Operation Temperature:-40°to+105°  
 Insulator Material:Polyester(UL94V-0)  
 Contact Material:Phosphor bronze  
 Standard:PA6T  
 Contact Plating:Gold Flash  
 Max.Processing Temp:240°C for30-60seconds  
 (260°C for5seconds)


P/N	PIN	DIM.A	DIM.B
PH1.0-02-01PWS	1	0.00	1.0
PH1.0-02-02PWS	2	1.0	2.00
PH1.0-02-03PWS	3	2.00	3.00
PH1.0-02-04PWS	4	3.00	4.00
PH1.0-02-05PWS	5	4.00	5.00
PH1.0-02-06PWS	6	5.00	6.00
PH1.0-02-07PWS	7	6.00	7.00
PH1.0-02-08PWS	8	7.00	8.00
PH1.0-02-09PWS	9	8.00	9.00
.....	.....	.....	.....
PH1.0-02-40PWS	40	(PIN-1)	(PIN)



PART NUMBER DESCRIPTION:

PH1.0-02-NPWS

(D=单排;S=双排)  
 (Z=直脚;W=弯脚)  
 (PIN数量;01.....50PIN)  
 (排针开关)



RECOMMEND P.C.B LAYOUT  
 PCB TOLERANCE:±0.05 (TOP VIEW)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:1.0PH H1.0 2xnPin SMT W2.3 PC5.0 PA2.0 PB1.4 L5.0 6T	
DECIMALS:	ANGLES:		PAR PH1.0-02-NPWS	
X.±0.30	X°±5'		DWN	
X.X±0.20	X.X°±1'		CHKD	
X.XX±0.10	X.XX°±0.5'	APVD		
CUSTOMER COPY		SCALE N:A	UNIT:MM	
		SIZE:A4	SHEET:1F1	
			REV:A	