






RoHS



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer PA66 PIN Brass Tin-plated

NP	A	B	NP	A	B
2P	6±0.2	2±0.15	10P	22±0.2	18±0.15
3P	8±0.2	4±0.15	11P	24±0.2	20±0.15
4P	10±0.2	6±0.15	12P	26±0.2	22±0.15
5P	12±0.2	8±0.15	13P	28±0.2	24±0.15
6P	14±0.2	10±0.15	14P	30±0.2	26±0.15
7P	16±0.2	12±0.15	15P	32±0.2	28±0.15
8P	18±0.2	14±0.15	16P	34±0.2	30±0.15
9P	20±0.2	16±0.15			

GENERL TOLERANCE		制 图	YUEWANG LIN			料 号 PART NO.	PH-NPW-M	版 本 REV.	A
X.±0.25	X.*±2°		审 核	PANJIN LI			品 名 TITLE	PH-CONNECTORS	
.X±0.20	.X*±1°	核 准		GUANBIN LUO			深圳市富港科技有限公司 SHENZHEN FUGANG TECHNOLOGY CO., LTD		
.XX±0.15	.XX*±0.5°								
.XXX±0.10	.XXX*±0.5°								
		单 位 UNITS	MM	比 例 SCALE	1:1				