





GT-TA035A-H0190-L2


Operating Force
B=250gf

Switch Height
H0190=1.90mm

Switch Lifetime (Force)
L2=200,000 Cycles



RECOMMENDED PCB LAYOUT



CIRCUIT DIAGRAM

G-Switch Specification:

Operating temperature range: -40℃to+85℃
Rating: 50mA, 12V DC
Insulation resistance: 100MΩ min. 100V DC
Dielectric strength: 250V AC for 1 min
Contact resistance: 100m Ω max.
Travel: 0.13±0.05mm
Waterproof Grade: IPX7



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.30
X.x ±0.20
X.xx ±0.15
X.xxx ±0.10
Angles ±3°

Title: Horizontal Tact Switch SMT
Sink0.94 2.8×1.9×1.9mm

Molde Code: GT-TA035A-H0190-L2

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.02.01

b-Switch 品赞科技®

REV: A0

SHEET: 1/1